

SCHOTT VG20, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT VG Glass (glass color will vary by product specification)

Stock **#16-946** CLEARANCE 10 TO 12 DAYS

- 1 +

₹23,659.65

ADD TO CART

Qty 1+

₹23,659.65

Volume Pricing

[Request Quote](#)

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.85

Glass/Filter Number:
[SCHOTT VG20](#)

Length (mm):
165.00

Coating:

Uncoated
Color: Green
Index of Refraction n_d: 1.54
Transformation Temperature (°C): 390
Thickness (mm): 4.50 ±0.5
Type: Bandpass Filter
Wavelength: UV-VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.91

Regulatory Compliance

Certificate of Conformance: View
--