

SCHOTT VG9, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT VG Glass (glass color will vary by product specification)

Stock **#16-945** 10 TO 12 DAYS

- 1 + **₹43,935.00**

ADD TO CART

Qty 1-10
₹43,935.00
Qty 11+
₹39,411.00
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.87

Glass/Filter Number:
[SCHOTT VG9](#)

Length (mm): 165.00
Coating: Uncoated
Color: Green
Index of Refraction n_d: 1.55
Transformation Temperature (°C): 462
Thickness (mm): 4.50 ±0.5
Type: Bandpass Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.91

Regulatory Compliance

Certificate of Conformance: View
--