

## Smart Vision Lights 75mm 850nm Bar Light



Stock **#90-436** NEW **1 In Stock**

-

1

+

 ₹47,634

Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹47,634 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                                                                                                                                                                                                                              |                       |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|
| LM75-850-W                                                                                                                                                                                                                           | Model Number:         |
| LED Illuminator                                                                                                                                                                                                                      | Type of Illumination: |
| <div>Note:<br/>5-Pin M12 cables sold separately (5m <a href="#">#23-951</a>, 10m <a href="#">#23-952</a>, 15m <a href="#">#23-953</a>)<br/>Industrial power supply for mounting to DIN rails also sold <a href="#">#75-579</a></div> |                       |
| Smart Vision Lights LLC                                                                                                                                                                                                              | Manufacturer:         |

|                                                                                                                                                                                                                                      |                             |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| Bar Light                                                                                                                                                                                                                            | Geometry:                   |
| Constant or Strobed                                                                                                                                                                                                                  | Illumination Mode:          |
| Physical & Mechanical Properties                                                                                                                                                                                                     |                             |
| 80.00 L x 34.00 W x 26.00 D                                                                                                                                                                                                          | Dimensions (mm):            |
| 256                                                                                                                                                                                                                                  | Weight (g):                 |
| 71.00 L x 25.5 W                                                                                                                                                                                                                     | Active Area (mm):           |
| Optical Properties                                                                                                                                                                                                                   |                             |
| NIR                                                                                                                                                                                                                                  | Color:                      |
| 850                                                                                                                                                                                                                                  | Wavelength (nm):            |
| 100 - 1000                                                                                                                                                                                                                           | Working Distance (mm):      |
| Electrical                                                                                                                                                                                                                           |                             |
| 30 - ∞                                                                                                                                                                                                                               | Strobe Duration (µs):       |
| Hardware & Interface Connectivity                                                                                                                                                                                                    |                             |
| 5-pin M12 connector                                                                                                                                                                                                                  | Connector:                  |
| 24 VDC ± 5%                                                                                                                                                                                                                          | Input Voltage (V):          |
| Power Supply:<br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#75-577</a><br>Europe: <a href="#">#75-578</a><br>Japan: <a href="#">#75-577</a><br>Korea: <a href="#">#75-579</a><br>China: <a href="#">#75-579</a> |                             |
| Threading & Mounting                                                                                                                                                                                                                 |                             |
| T-Slot for M6 Nut                                                                                                                                                                                                                    | Mount:                      |
| Environmental & Durability Factors                                                                                                                                                                                                   |                             |
| -10° to +40°                                                                                                                                                                                                                         | Operating Temperature (°C): |
| Regulatory Compliance                                                                                                                                                                                                                |                             |
| <a href="#">View</a>                                                                                                                                                                                                                 | Certificate of Conformance: |
| United States                                                                                                                                                                                                                        | Country of Origin:          |
| Edmund Optics India Private Limited                                                                                                                                                                                                  | Imported By:                |

## Product Details

- Compact Bar Lights Available In 45mm Or 75mm Lengths
- Delivers up to 73,000 (for the 75mm) and 44,000 (45mm) lux with Strobing
- Available In White, Blue, Green, Red, Or IR Wavelengths
- Ideal For Space-Constrained Imaging Applications

Smart Vision Lights LMMini Bar Lights are compact linear lights that are designed to deliver intense light for space-constrained applications and feature IP65 rating for dust and water protection. These lights are available in 45 or 75mm lengths in white, blue (470nm), green (530nm), red (635), or IR (850nm) wavelengths. Built in Multi-Drive™ technology allows for these lights to operate in continuous mode for standard operation or strobe mode for high speed or increased brightness needs. Smart Vision Lights LMMini Bar Lights are recommended to use at a working distance of 100 – 1000mm. Optional mounting brackets are sold separately and can be used to configure the lights in a quad formation to illuminate a larger area.