

TECHSPEC® T-Mount Aperture Cap



#66-037: T-Mount Aperture Cap

Stock **#66-037** **5 In Stock**

1 MRP ₹3,204

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹3,204 each
Qty 5-9	₹2,865 each
Qty 10-25	₹2,694 each
Need More?	Request Quote

Product Downloads

General

Tube Cap **Function:**

Physical & Mechanical Properties

5.0 **Total Length (mm):**

Thickness (mm):

4.00

Extension Length (mm):

54.5

Threading & Mounting

Thread Type:

T-Mount

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

Technical Information

