

12.5/12.7mm Optic Dia., Top Adjust Kinematic Mount, Micrometer



Stock #13-769 **5 In Stock**

₹19,805

ADD TO CART

Volume Pricing

Qty 1-4	₹19,805 each
Qty 5+	₹18,822 each
Need More?	Request Quote

Product Downloads

General

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Type of Adjustment Screws:
Micrometer

Physical & Mechanical Properties

Clear Aperture CA (mm):
11.0

±2.5 Fine Tilt Angle (°):

±2.5 Fine Tip Angle (°):

3.0 Min. Thickness of Compatible Optics (mm):

Threading & Mounting

12.5 - 12.7 Size of Compatible Optics (mm):

M6 x 1.0 Compatible Post:

Regulatory Compliance

Exempt RoHS 2015:

View Certificate of Conformance:

Contains SVHC(s) Reach 247:

Japan Country of Origin:


Edmund Optics India Private Limited Imported By:

Product Details

- Micrometer or Lead Screw Driven Tip-Tilt Adjustment
- Color Coded Knobs for Tip and Tilt
- Set Screws and Delrin® Pads Hold Optical Component in Place
- Posts and Post Holders Required for Mounting

Top Adjustment Kinematic Mounts attach to posts or other optomechanics to securely hold optical components in place. Micrometers or adjustment screws are positioned at the top of the mounts to avoid interfering with system placement. The M6 mounting hole is positioned to where the first surface of the mounted mirror is as close to the post centerline as possible. Top Adjustment Kinematic Mounts are constructed of black anodized aluminum. Posts and Post Holders are required for mounting to a breadboard.

Technical Information



Optic Diameter D1 (mm)	Clear Aperture, D2 (mm)	A (mm)	B (mm)	C (mm)	Stock No.
25.00	22.00	60.00	30.00	36.00	#56-327 #56-238*
25.40	22.00	60.00	30.00	36.00	#55-003 #55-456*
50.80	47.00	80.00	40.00	56.00	#55-005 #56-326*
50.00	47.00	80.00	40.00	56.00	#55-457*

* with micrometer

