

Top-Screw Model, Threaded Base - Metric Mirror Mount



Stock **#56-343** 17 In Stock

-

1

+

₹12,763

ADD TO CART

Volume Pricing	
Qty 1-4	₹12,763 each
Qty 5-9	₹11,303 each
Qty 10-25	₹10,416 each
Need More?	Request Quote

Product Downloads

General	
Adjustable - Tip-Tilt	Type:
Square or Rectangular	Type of Optics:

Physical & Mechanical Properties	
0.11	Weight (kg):

Black Anodized Aluminum, Stainless Steel	Construction:
±3	Fine Tilt Angle (°):
±3	Fine Tip Angle (°):
Top	Adjustment Screw Position:
0.25	Resolution (mm):

Threading & Mounting	
3.0 - 25.4	Size of Compatible Optics (mm):
M6 x 1.0	Compatible Post:

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Two-Axis Tilt Control
- 25mm Square Mounting Surfaces
- Back or Top Screw Options
- Slotted or Threaded Based Options
- Black Anodized Aluminum
- [Posts](#) and [Post Holders](#) Required for Mounting

These micro-sized Mirror Mounts are ideal for use in restricted spaces. Each offers a 25mm square mounting surface. Adjustment screws have 0.25mm pitch thread for fine angular resolution. Precision tilting of the mounting surface in two axes can be done with either top screw or standard (screws in back) model options. 25mm square or diameter first surface mirrors can be easily bonded using our wide range of optical adhesives. Metric mounting holes allow for a wide range of integration solutions. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

Technical Information

