



Hoya U330 (UV) 12mm Dia., Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#46-095** 7 DAYS
[Additional Bandwidths](#)

-

1

+

₹3,567.00

ADD TO CART

Qty 1-10
₹3,567.00
Qty 11+
₹3,219.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.00

Center Wavelength CWL (nm):

330.00
Density (g/cm³): 2.78
Full Width-Half Max FWHM (nm): 140.00
Glass/Filter Number: Hoya U330
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Black
Surface Quality: 60-40
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: UV
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View