

UV, 4" High Brightness LED Diffuse Axial Illuminator

See More by [Advanced Illumination](#)



Advanced Illumination Diffuse Axial LED Illuminators

Stock **#91-064** NEW CONTACT US

-

1

+

₹2,23,590

ADD TO CART

Volume Pricing	
Qty 1+	₹2,23,590 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
DL225-100365IC	Model Number:
LED Illuminator	Type of Illumination:
	Manufacturer:

Advanced Illumination	
Diffuse Axial	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
177 L x 110 W x 113 T	Dimensions (mm):
1396.2	Weight (g):
~4" x 4"	Aperture Size:
Optical Properties	
UV	Color:
395.00	Wavelength (nm):
25	Working Distance (mm):
Hardware & Interface Connectivity	
Flying Leads	Connector:
Power Supply:	
Power Supply Required and Sold Separately:	
USA: #66-855	
Europe: #66-855	
Japan: #89-513	
Korea: #33-773	
China: #66-855	
Environmental & Durability Factors	
0 to +60	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Bright, Consistent Diffuse Illumination Over Field of View
- Unique Modular Heat Sink Design
- Internal Beamsplitter Ideal for Inspecting Highly Reflective Objects
- Excellent Light Stability

Advanced Illumination Diffuse Axial LED Illuminators are ideal for inspecting highly reflective optics. These coaxial illuminators provide even illumination over the field coverage. Advanced Illumination Diffuse Axial LED Illuminators feature vibration free performance and easily mount via M6 threaded holes.

Note: Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately. Units cannot be intensity controlled.

TECHNICAL INFORMATION

