

[See all 14 Products in Family](#)

UV-VIS Heavy-Duty Transmission Dip Probe

See More by [Ocean Optics](#)



Stock #90-569 **NEW** 1 In Stock

- 1 + ₹2,26,365

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,26,365 each
Need More?	Request Quote

Product Downloads

SMA905 **Fiber Connector Type:**

General

T1300-UV-VIS **Model Number:**

Breakout 1 meter from end of the probe **Note:**

UV-VIS Heavy-Duty Transmission Dip Probe **Title:**

Optical Properties

Wavelength Range (nm):
200 - 1100

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV-VIS to MS-NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).

Technical Information

Transmission Dip Probe	Transmission Dip Probe Stock Number	Compatible Transmission Dip Probe Tip	Compatible Transmission Dip Probe Tip Stock Number
UV-MS Heavy-Duty Transmission Dip Probe	#90-569	Harsh Environment Transmission Dip Probe Tip, 2 mm	#90-582
		Harsh Environment Transmission Dip Probe Tip, 5 mm	#90-584
		Harsh Environment Transmission Dip Probe Tip, 10 mm	#90-580
		Harsh Environment Transmission Dip Probe Tip, 25 mm	#90-581
		Harsh Environment Transmission Dip Probe Tip, 50 mm	#90-583
UV-MS Transmission Dip Probe	#90-570	Stainless Steel Transmission Dip Probe Tip, 2 mm	#90-573
		Stainless Steel Transmission Dip Probe Tip, 5 mm	#90-576
		Stainless Steel Transmission Dip Probe Tip, 10 mm	#90-572
		Adjustable Path Length Transmission Dip Probe Tip, 2–10 mm	#90-578
		Adjustable Path Length Transmission Dip Probe Tip, 10–20 mm	#90-577
		Stainless Steel Transmission Dip Probe Tip, 2 mm	#90-573
		Stainless Steel Transmission Dip Probe Tip, 5 mm	#90-576

MS-NIR Transmission Dip Probe	#90-571	Stainless Steel Transmission Dip Probe Tip, 10 mm	#90-572
		Adjustable Path Length Transmission Dip Probe Tip, 2–10 mm	#90-578
		Adjustable Path Length Transmission Dip Probe Tip, 10–20 mm	#90-577

;