

White Mi-LED Fiber Optic LED Illuminator

See More by [Dolan-Jenner](#)



#89-740

Stock **#89-740** **2 In Stock**

MRP ₹79,650

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹79,650 each
Qty 6+	₹71,685 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

40,000 **Operating Lifetime (hours):**

Variable 10-100% **Intensity Control Option:**

Fan Cooled **Cooling Method:**

Type of Illumination:	Fiber Optic Illuminator, LED
Compatible Light Guide Adapter:	25mm Interface: MX (Preferred), SX for semi-rigid light guides or hybrid light guides
Manufacturer:	Dolan-Jenner

Illumination Mode:	Constant
---------------------------	----------

Physical & Mechanical Properties

Dimensions (inches):	7.0 x 4.9 x 8.8
Dimensions (mm):	177.8 x 124.46 x 223.52
Weight (lbs):	6.00
Weight (kg):	2.72

Housing:	High Impact Polymer, Stackable
-----------------	--------------------------------

Optical Properties

Color:	White
---------------	-------

Electrical

Output Power (Lumens):	2000+ (12.7mm aperture)
-------------------------------	-------------------------

Hardware & Interface Connectivity

Input Voltage (V):	100-240 VAC 50/60 Hz
---------------------------	----------------------

Environmental & Durability Factors

Operating Temperature (°C):	5 to 40
Color Temperature (K):	5000.00

Regulatory Compliance

Reach 174:	Compliant
Certificate of Conformance:	View

Country of Origin:	United States
Imported By:	Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000

Product Details

- 10 – 100% Solid State Variable Intensity
- 40,000 Hour LED Life
- Iris Option Available

Dolan-Jenner M-LED Fiber Optic LED Illuminators have been optimized for exceptional performance, low energy consumption, and long operating lifetimes. When compared to conventional 150 watt halogen illuminators, Dolan-Jenner M-LED Fiber Optic LED Illuminators provide greater intensity, consume less than half the energy, and do not require lamp replacements. The illuminator's LEDs already operate at 5000K color temperature and do not require additional IR filters. Additionally, the low energy consumption allows for estimated lifetimes of 40,000 hours. These illuminators also feature quiet performance, low noise levels, and 100 – 240 volt universal voltage. Multiple noises pieces are available for added adaptability.

Note: Dolan-Jenner [Fiber Optic Adapters](#) (sold separately) are required to mate with fiber optic light guides. SX adapters are required if using a single or dual branch semi-rigid light guide or [hybrid light guides](#).