

# White, Strobed, 3.0" LED Line Light

See More by [Advanced Illumination](#)



Stock **#83-282** [CONTACT US](#)

-

1

+

**₹67,077.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1+                        |
| ₹67,077.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

- Color:**  
White
- Model Number:**  
LL2912A-WHI-I3
- Mount:**  
Via (2) M2 Screws
- Operating Temperature (°C):**  
0 to 65

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Dimensions (mm):</b><br>101 L x61 Wx24 D                                                                                                                                                                                                 |
| <b>Working Distance (mm):</b><br>25.4                                                                                                                                                                                                       |
| <b>LED Lifetime (hours):</b><br>100,000                                                                                                                                                                                                     |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#66-855</a><br>Europe: <a href="#">#66-855</a><br>Japan: <a href="#">#66-855</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#66-855</a> |
| <b>Light Distribution (%):</b><br>±5 Over Illuminated Area (Dependent on Working Distance)                                                                                                                                                  |
| <b>Number of LEDs:</b><br>12.00                                                                                                                                                                                                             |
| <b>Number of Channels:</b><br>1.00                                                                                                                                                                                                          |
| <b>Field Coverage (mm):</b><br>6.35 thick                                                                                                                                                                                                   |
| <b>Maximum Trigger Frequency (Hz):</b><br>30.00                                                                                                                                                                                             |
| <b>Strobe Duration (µs):</b><br>30 - 300                                                                                                                                                                                                    |
| <b>Type of Illumination:</b><br>LED Illuminator                                                                                                                                                                                             |
| <b>Note:</b><br>Optional Manual Intensity Adjustment <a href="#">#86-887</a> and <a href="#">#89-555</a> are Available                                                                                                                      |
| <b>Manufacturer:</b><br>Advanced Illumination                                                                                                                                                                                               |
| <b>Geometry:</b><br>Line Light                                                                                                                                                                                                              |
| <b>Illumination Mode:</b><br>Strobed                                                                                                                                                                                                        |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Contains SVHC(s)</a>      |