

White, Strobed, Extended Working Distance 4" LED Ring Light w/ Barrel Mount

See More by [Advanced Illumination](#)



Stock #83-246

CONTACT US

-

1

+

₹85,782.00

ADD TO CART

Qty 1+

₹85,782.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:

White

Diameter (mm):

100.00

Inner Diameter (mm):

55.5

Model Number:

RL4260B-WHIEDF-IS

Mount: 3 screw Barrel Mount
Operating Temperature (°C): 0 to 65
Outer Diameter (mm): 100.00
Mounting Threads: M4 x4
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of LEDs: 60.00
Number of Channels: 1.00
Field Coverage (mm): 50.8 (2")
Strobe Duration (µs): 30 - 300
Type of Illumination: LED Illuminator
Note: Requires a 24V power supply #66-855 . European power supply #35-200 also available.
Manufacturer: Advanced Illumination
Geometry: Ring Light
Illumination Mode: Strobed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View