

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Convex \(PCX\) Lenses](#) / [Standard Plano-Convex \(PCX\) Lenses](#)

TECHSPEC® VIS-NIR Coated Plano-Convex (PCX) Lenses



- AR Coated to Provide <1.25% Reflectance per Surface for 400 - 1000nm
- <0.25% Reflectance @ 880nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#)

Common Specifications

Physical & Mechanical Properties

Bevel: Protective as needed



Optical Properties

Coating: VIS-NIR (400-1000nm)

Focal Length Tolerance (%): ± 1

Wavelength Range (nm): 400 - 1000

Technical Information



Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
1.00	0.60	0.17	VIS-NIR (400-1000nm)	N-LASF9	#65-289	₹6,345 Volume Pricing	5 In Stock
1.00	1.00	0.57	VIS-NIR (400-1000nm)	N-LASF9	#65-290	₹6,345 Volume Pricing	5 In Stock
1.00	1.50	1.07	VIS-NIR (400-1000nm)	N-LASF9	#65-291	₹6,345 Volume Pricing	Contact Us
1.00	2.00	1.57	VIS-NIR (400-1000nm)	N-LASF9	#65-292	₹6,345 Volume Pricing	6 In Stock
1.50	1.00	0.57	VIS-NIR (400-1000nm)	N-LASF9	#65-293	₹6,345 Volume Pricing	5 In Stock
1.50	1.50	1.07	VIS-NIR (400-1000nm)	N-LASF9	#65-294	₹6,345 Volume Pricing	3 In Stock
1.50	2.00	1.57	VIS-NIR (400-1000nm)	N-LASF9	#65-295	₹6,345 Volume Pricing	17 In Stock
2.00	1.50	1.07	VIS-NIR (400-1000nm)	N-LASF9	#65-296	₹6,267 Volume Pricing	20+ In Stock
2.00	2.00	1.57	VIS-NIR (400-1000nm)	N-LASF9	#65-297	₹6,267 Volume Pricing	20+ In Stock
2.00	3.00	2.57	VIS-NIR (400-1000nm)	N-LASF9	#65-298	₹6,267 Volume Pricing	5 In Stock
2.00	4.00	3.57	VIS-NIR (400-1000nm)	N-LASF9	#65-299	₹6,267 Volume Pricing	4 In Stock
2.50	2.00	1.57	VIS-NIR (400-1000nm)	N-LASF9	#65-300	₹6,267 Volume Pricing	2 In Stock

2.50	2.50	2.05	VIS-NIR (400-1000nm)	N-LASF9	#65-301	₹6,267 Volume Pricing	10 In Stock
2.50	3.00	2.57	VIS-NIR (400-1000nm)	N-LASF9	#65-302	₹6,267 Volume Pricing	20+ In Stock
2.50	4.00	3.57	VIS-NIR (400-1000nm)	N-LASF9	#65-303	₹6,267 Volume Pricing	10 In Stock
2.50	5.00	4.57	VIS-NIR (400-1000nm)	N-LASF9	#65-304	₹6,267 Volume Pricing	13 In Stock
3.00	3.00	1.88	VIS-NIR (400-1000nm)	N-SF11	#49-174	₹5,372 Volume Pricing	7 In Stock
3.00	4.50	3.50	VIS-NIR (400-1000nm)	N-LASF44	#49-175	₹5,372 Volume Pricing	20+ In Stock
3.00	6.00	4.81	VIS-NIR (400-1000nm)	N-BK7	#49-176	₹4,982 Volume Pricing	3 In Stock
3.00	7.50	6.51	VIS-NIR (400-1000nm)	N-BK7	#49-177	₹4,982 Volume Pricing	20+ In Stock
3.00	9.00	8.01	VIS-NIR (400-1000nm)	N-BK7	#49-178	₹4,982 Volume Pricing	20+ In Stock
3.00	12.00	11.29	VIS-NIR (400-1000nm)	N-BK7	#49-179	₹4,982 Volume Pricing	10 In Stock
3.00	15.00	14.17	VIS-NIR (400-1000nm)	N-BK7	#49-180	₹4,982 Volume Pricing	5 In Stock
4.00	4.00	3.06	VIS-NIR (400-1000nm)	N-LASF44	#47-850	₹5,372 Volume Pricing	8 In Stock
4.00	6.00	4.51	VIS-NIR (400-1000nm)	N-BK7	#47-851	₹5,372 Volume Pricing	20+ In Stock
4.00	8.00	7.17	VIS-NIR (400-1000nm)	N-BAF10	#47-852	₹5,060 Volume Pricing	Contact Us

4.00	10.00	8.92	VIS-NIR (400-1000nm)	N-BK7	#47-853	₹5,060 Volume Pricing	20+ In Stock
4.00	12.00	11.00	VIS-NIR (400-1000nm)	N-BK7	#47-854	₹5,060 Volume Pricing	Contact Us
4.50	4.50	3.05	VIS-NIR (400-1000nm)	N-LASF44	#47-855	₹5,372 Volume Pricing	20+ In Stock
4.50	9.00	7.41	VIS-NIR (400-1000nm)	N-BK7	#47-856	₹5,060 Volume Pricing	7 In Stock
5.00	5.00	3.96	VIS-NIR (400-1000nm)	N-LASF44	#47-857	₹3,951 Volume Pricing	20+ In Stock
5.00	7.50	6.43	VIS-NIR (400-1000nm)	N-SF11	#48-661	₹3,912 Volume Pricing	13 In Stock
5.00	10.00	8.91	VIS-NIR (400-1000nm)	N-BK7	#47-858	₹3,912 Volume Pricing	2 In Stock
5.00	12.00	10.83	VIS-NIR (400-1000nm)	N-BK7	#47-859	₹3,912 Volume Pricing	6 In Stock
5.00	15.00	13.94	VIS-NIR (400-1000nm)	N-BK7	#47-860	₹3,912 Volume Pricing	Contact Us
5.00	20.00	19.02	VIS-NIR (400-1000nm)	N-BK7	#49-913	₹3,912 Volume Pricing	5 In Stock
5.00	25.00	23.95	VIS-NIR (400-1000nm)	N-BK7	#87-917	₹3,912 Volume Pricing	2 In Stock
5.00	30.00	28.95	VIS-NIR (400-1000nm)	N-BK7	#87-918	₹3,912 Volume Pricing	1 In Stock
6.00	6.00	4.60	VIS-NIR (400-1000nm)	N-SF11	#45-465	₹3,309 Volume Pricing	1 In Stock
6.00	7.50	6.10	VIS-NIR (400-1000nm)	N-SF11	#49-914	₹3,270 Volume Pricing	Contact Us

6.00	9.00	7.95	VIS-NIR (400-1000nm)	N-SF5	#45-466	₹3,270 Volume Pricing	20+ In Stock
6.00	10.00	8.82	VIS-NIR (400-1000nm)	N-BK7	#38-483	₹3,270 Volume Pricing	6 In Stock
6.00	12.00	10.94	VIS-NIR (400-1000nm)	N-BK7	#45-467	₹3,192 Volume Pricing	20+ In Stock
6.00	15.00	13.68	VIS-NIR (400-1000nm)	N-BK7	#45-468	₹3,192 Volume Pricing	20+ In Stock
6.00	18.00	17.07	VIS-NIR (400-1000nm)	N-BK7	#45-469	₹3,192 Volume Pricing	8 In Stock
6.00	20.00	19.04	VIS-NIR (400-1000nm)	N-BK7	#38-484	₹3,192 Volume Pricing	5 In Stock
6.00	21.00	20.06	VIS-NIR (400-1000nm)	N-BK7	#45-470	₹3,192 Volume Pricing	20+ In Stock
6.00	24.00	23.01	VIS-NIR (400-1000nm)	N-BK7	#45-471	₹3,192 Volume Pricing	20+ In Stock
6.00	25.00	24.04	VIS-NIR (400-1000nm)	N-BK7	#38-485	₹3,192 Volume Pricing	4 In Stock
6.00	30.00	29.14	VIS-NIR (400-1000nm)	N-BK7	#45-472	₹3,192 Volume Pricing	8 In Stock
6.00	36.00	34.95	VIS-NIR (400-1000nm)	N-BK7	#45-473	₹3,192 Volume Pricing	2 In Stock
6.00	48.00	46.95	VIS-NIR (400-1000nm)	N-BK7	#47-381	₹3,192 Volume Pricing	1 In Stock
6.00	60.00	58.95	VIS-NIR (400-1000nm)	N-BK7	#67-178	₹3,192 Volume Pricing	7 In Stock
6.00	72.00	70.97	VIS-NIR (400-1000nm)	N-BK7	#45-696	₹3,192 Volume Pricing	6 In Stock

7.00	7.00	5.50	VIS-NIR (400-1000nm)	N-SF11	#71-298	₹3,270 Volume Pricing	Contact Us
7.00	10.00	8.10	VIS-NIR (400-1000nm)	N-BK7	#71-305	₹3,231 Volume Pricing	6 In Stock
7.00	12.00	10.30	VIS-NIR (400-1000nm)	N-BK7	#71-312	₹3,231 Volume Pricing	5 In Stock
8.00	8.00	6.40	VIS-NIR (400-1000nm)	N-SF11	#71-319	₹3,270 Volume Pricing	Contact Us
8.00	10.00	7.60	VIS-NIR (400-1000nm)	N-BK7	#71-326	₹3,231 Volume Pricing	5 In Stock
8.00	12.00	10.00	VIS-NIR (400-1000nm)	N-BK7	#71-333	₹3,231 Volume Pricing	4 In Stock
9.00	9.00	7.32	VIS-NIR (400-1000nm)	N-SF11	#45-474	₹3,348 Volume Pricing	Contact Us
9.00	10.00	8.49	VIS-NIR (400-1000nm)	N-SF11	#38-486	₹3,348 Volume Pricing	Contact Us
9.00	12.00	10.60	VIS-NIR (400-1000nm)	N-SF11	#49-915	₹3,348 Volume Pricing	1 In Stock
9.00	13.50	11.94	VIS-NIR (400-1000nm)	N-SF5	#45-475	₹3,348 Volume Pricing	20+ In Stock
9.00	15.00	13.02	VIS-NIR (400-1000nm)	N-BK7	#49-916	₹3,348 Volume Pricing	20+ In Stock
9.00	18.00	16.41	VIS-NIR (400-1000nm)	N-BK7	#45-476	₹3,270 Volume Pricing	20+ In Stock
9.00	20.00	18.55	VIS-NIR (400-1000nm)	N-BK7	#38-487	₹3,270 Volume Pricing	15 In Stock
9.00	22.00	20.73	VIS-NIR (400-1000nm)	N-BK7	#45-477	₹3,270 Volume Pricing	9 In Stock

9.00	25.00	23.68	VIS-NIR (400-1000nm)	N-BK7	#38-488	₹3,270 Volume Pricing	20+ In Stock
9.00	27.00	25.34	VIS-NIR (400-1000nm)	N-BK7	#45-478	₹3,270 Volume Pricing	7 In Stock
9.00	36.00	34.48	VIS-NIR (400-1000nm)	N-BK7	#45-479	₹3,270 Volume Pricing	20+ In Stock
9.00	45.00	43.98	VIS-NIR (400-1000nm)	N-BK7	#45-703	₹3,270 Volume Pricing	1 In Stock
9.00	54.00	52.69	VIS-NIR (400-1000nm)	N-BK7	#67-179	₹3,270 Volume Pricing	3 In Stock
9.00	72.00	70.68	VIS-NIR (400-1000nm)	N-BK7	#67-180	₹3,270 Volume Pricing	2 In Stock
9.00	90.00	88.68	VIS-NIR (400-1000nm)	N-BK7	#67-181	₹3,270 Volume Pricing	1 In Stock
10.00	10.00	8.18	VIS-NIR (400-1000nm)	N-SF11	#63-519	₹3,348 Volume Pricing	Contact Us
10.00	15.00	13.32	VIS-NIR (400-1000nm)	N-SF11	#63-520	₹3,348 Volume Pricing	20+ In Stock
10.00	20.00	18.03	VIS-NIR (400-1000nm)	N-BK7	#63-521	₹3,270 Volume Pricing	20+ In Stock
10.00	25.00	23.02	VIS-NIR (400-1000nm)	N-BK7	#63-522	₹3,270 Volume Pricing	9 In Stock
10.00	30.00	28.01	VIS-NIR (400-1000nm)	N-BK7	#63-523	₹3,270 Volume Pricing	9 In Stock
10.00	40.00	38.02	VIS-NIR (400-1000nm)	N-BK7	#63-524	₹3,270 Volume Pricing	11 In Stock
10.00	50.00	48.02	VIS-NIR (400-1000nm)	N-BK7	#63-525	₹3,270 Volume Pricing	2 In Stock

10.00	75.00	73.02	VIS-NIR (400-1000nm)	N-BK7	#63-526	₹3,270 Volume Pricing	Contact Us
10.00	100.00	98.02	VIS-NIR (400-1000nm)	N-BK7	#63-527	₹3,270 Volume Pricing	20+ In Stock
12.00	12.00	9.76	VIS-NIR (400-1000nm)	N-SF11	#45-480	₹3,620 Volume Pricing	20+ In Stock
12.00	15.00	12.03	VIS-NIR (400-1000nm)	N-BK7	#45-481	₹3,620 Volume Pricing	20+ In Stock
12.00	18.00	16.22	VIS-NIR (400-1000nm)	N-SF5	#45-482	₹3,620 Volume Pricing	20+ In Stock
12.00	20.00	17.69	VIS-NIR (400-1000nm)	N-BK7	#49-917	₹3,620 Volume Pricing	4 In Stock
12.00	24.00	22.15	VIS-NIR (400-1000nm)	N-BK7	#45-483	₹3,542 Volume Pricing	5 In Stock
12.00	30.00	28.02	VIS-NIR (400-1000nm)	N-BK7	#45-484	₹3,542 Volume Pricing	20+ In Stock
12.00	36.00	34.02	VIS-NIR (400-1000nm)	N-BK7	#33-355	₹3,542 Volume Pricing	12 In Stock
12.00	42.00	40.22	VIS-NIR (400-1000nm)	N-BK7	#45-485	₹3,542 Volume Pricing	20+ In Stock
12.00	48.00	46.36	VIS-NIR (400-1000nm)	N-BK7	#45-486	₹3,542 Volume Pricing	20+ In Stock
12.00	54.00	52.02	VIS-NIR (400-1000nm)	N-BK7	#45-487	₹3,542 Volume Pricing	14 In Stock
12.00	60.00	58.37	VIS-NIR (400-1000nm)	N-BK7	#45-488	₹3,542 Volume Pricing	20+ In Stock
12.00	72.00	70.42	VIS-NIR (400-1000nm)	N-BK7	#45-705	₹3,542 Volume Pricing	4 In Stock

12.00	84.00	82.39	VIS-NIR (400-1000nm)	N-BK7	#45-489	₹3,542 Volume Pricing	20+ In Stock
12.00	100.00	98.35	VIS-NIR (400-1000nm)	N-BK7	#45-490	₹3,542 Volume Pricing	20+ In Stock
12.50	17.50	15.00	VIS-NIR (400-1000nm)	N-BK7	#38-501	₹3,542 Volume Pricing	2 In Stock
12.50	35.00	33.42	VIS-NIR (400-1000nm)	N-BK7	#38-506	₹3,464 Volume Pricing	4 In Stock
12.70	12.70	10.46	VIS-NIR (400-1000nm)	N-SF11	#62-591	₹3,542 Volume Pricing	20+ In Stock
12.70	15.00	11.53	VIS-NIR (400-1000nm)	N-BK7	#62-592	₹3,542 Volume Pricing	8 In Stock
12.70	19.10	16.46	VIS-NIR (400-1000nm)	N-BK7	#62-593	₹3,542 Volume Pricing	4 In Stock
12.70	20.00	17.49	VIS-NIR (400-1000nm)	N-BK7	#38-515	₹3,542 Volume Pricing	Contact Us
12.70	25.40	23.43	VIS-NIR (400-1000nm)	N-BK7	#62-594	₹3,464 Volume Pricing	16 In Stock
12.70	30.00	28.22	VIS-NIR (400-1000nm)	N-BK7	#38-516	₹3,464 Volume Pricing	4 In Stock
12.70	31.80	29.81	VIS-NIR (400-1000nm)	N-BK7	#62-595	₹3,464 Volume Pricing	20+ In Stock
12.70	38.10	36.12	VIS-NIR (400-1000nm)	N-BK7	#62-596	₹3,464 Volume Pricing	20+ In Stock
12.70	40.00	38.48	VIS-NIR (400-1000nm)	N-BK7	#38-517	₹3,464 Volume Pricing	12 In Stock
12.70	44.50	42.69	VIS-NIR (400-1000nm)	N-BK7	#62-597	₹3,464 Volume Pricing	3 In Stock

12.70	50.80	49.15	VIS-NIR (400-1000nm)	N-BK7	#62-598	₹3,464 Volume Pricing	Contact Us
15.00	15.00	11.71	VIS-NIR (400-1000nm)	N-SF5	#45-491	₹3,620 Volume Pricing	20+ In Stock
15.00	18.00	15.61	VIS-NIR (400-1000nm)	N-SF5	#49-918	₹3,620 Volume Pricing	20+ In Stock
15.00	20.00	17.74	VIS-NIR (400-1000nm)	N-SF5	#63-528	₹3,620 Volume Pricing	5 In Stock
15.00	22.50	20.50	VIS-NIR (400-1000nm)	N-SF5	#45-492	₹3,620 Volume Pricing	20+ In Stock
15.00	30.00	27.90	VIS-NIR (400-1000nm)	N-BK7	#45-493	₹3,542 Volume Pricing	20+ In Stock
15.00	40.00	38.02	VIS-NIR (400-1000nm)	N-BK7	#45-494	₹3,542 Volume Pricing	17 In Stock
15.00	45.00	43.35	VIS-NIR (400-1000nm)	N-BK7	#49-919	₹3,542 Volume Pricing	5 In Stock
15.00	60.00	58.65	VIS-NIR (400-1000nm)	N-BK7	#47-382	₹3,542 Volume Pricing	20+ In Stock
15.00	75.00	73.79	VIS-NIR (400-1000nm)	N-BK7	#47-383	₹3,542 Volume Pricing	20+ In Stock
15.00	100.00	98.02	VIS-NIR (400-1000nm)	N-BK7	#45-706	₹3,542 Volume Pricing	20+ In Stock
15.00	200.00	197.89	VIS-NIR (400-1000nm)	N-BK7	#14-380	₹3,542 Volume Pricing	2 In Stock
15.00	250.00	248.02	VIS-NIR (400-1000nm)	N-BK7	#14-388	₹3,542 Volume Pricing	Contact Us
18.00	18.00	15.20	VIS-NIR (400-1000nm)	N-SF11	#48-426	₹3,737 Volume Pricing	20+ In Stock

18.00	22.50	20.26	VIS-NIR (400-1000nm)	N-SF11	#49-920	₹3,698 Volume Pricing	20+ In Stock
18.00	27.00	24.73	VIS-NIR (400-1000nm)	N-SF5	#45-495	₹3,698 Volume Pricing	20+ In Stock
18.00	36.00	33.65	VIS-NIR (400-1000nm)	N-BK7	#45-496	₹3,581 Volume Pricing	20+ In Stock
18.00	54.00	52.02	VIS-NIR (400-1000nm)	N-BK7	#45-497	₹3,581 Volume Pricing	3 In Stock
18.00	72.00	70.05	VIS-NIR (400-1000nm)	N-BK7	#45-498	₹3,581 Volume Pricing	20+ In Stock
20.00	20.00	17.42	VIS-NIR (400-1000nm)	N-SF11	#45-499	₹3,776 Volume Pricing	20+ In Stock
20.00	25.00	22.76	VIS-NIR (400-1000nm)	N-SF11	#49-921	₹3,737 Volume Pricing	20+ In Stock
20.00	30.00	27.30	VIS-NIR (400-1000nm)	N-BAF10	#45-707	₹3,737 Volume Pricing	20+ In Stock
20.00	35.00	32.04	VIS-NIR (400-1000nm)	N-BK7	#49-922	₹3,737 Volume Pricing	Contact Us
20.00	40.00	36.77	VIS-NIR (400-1000nm)	N-BK7	#45-500	₹3,620 Volume Pricing	20+ In Stock
20.00	50.00	47.87	VIS-NIR (400-1000nm)	N-BK7	#45-501	₹3,620 Volume Pricing	20+ In Stock
20.00	60.00	57.03	VIS-NIR (400-1000nm)	N-BK7	#45-502	₹3,620 Volume Pricing	20+ In Stock
20.00	70.00	68.03	VIS-NIR (400-1000nm)	N-BK7	#45-503	₹3,620 Volume Pricing	14 In Stock
20.00	80.00	78.45	VIS-NIR (400-1000nm)	N-BK7	#47-385	₹3,620 Volume Pricing	14 In Stock

20.00	100.00	97.13	VIS-NIR (400-1000nm)	N-BK7	#45-708	₹3,620 Volume Pricing	Contact Us
20.00	150.00	148.02	VIS-NIR (400-1000nm)	N-BK7	#47-386	₹3,620 Volume Pricing	4 In Stock
25.00	25.00	20.22	VIS-NIR (400-1000nm)	N-SF5	#45-504	₹3,970 Volume Pricing	20+ In Stock
25.00	30.00	24.69	VIS-NIR (400-1000nm)	N-BK7	#45-505	₹3,970 Volume Pricing	5 In Stock
25.00	35.00	30.42	VIS-NIR (400-1000nm)	N-BK7	#45-506	₹3,970 Volume Pricing	15 In Stock
25.00	40.00	36.31	VIS-NIR (400-1000nm)	N-BK7	#45-507	₹3,970 Volume Pricing	20+ In Stock
25.00	50.00	46.75	VIS-NIR (400-1000nm)	N-BK7	#45-508	₹3,815 Volume Pricing	20+ In Stock
25.00	60.00	56.90	VIS-NIR (400-1000nm)	N-BK7	#45-509	₹3,815 Volume Pricing	5 In Stock
25.00	75.00	72.00	VIS-NIR (400-1000nm)	N-BK7	#45-510	₹3,815 Volume Pricing	20+ In Stock
25.00	85.00	82.17	VIS-NIR (400-1000nm)	N-BK7	#45-511	₹3,815 Volume Pricing	Contact Us
25.00	100.00	97.13	VIS-NIR (400-1000nm)	N-BK7	#45-512	₹3,815 Volume Pricing	20+ In Stock
25.00	125.00	122.70	VIS-NIR (400-1000nm)	N-BK7	#45-513	₹3,815 Volume Pricing	13 In Stock
25.00	150.00	147.81	VIS-NIR (400-1000nm)	N-BK7	#45-514	₹3,815 Volume Pricing	20+ In Stock
25.00	175.00	172.85	VIS-NIR (400-1000nm)	N-BK7	#45-515	₹3,815 Volume Pricing	13 In Stock

25.00	200.00	197.89	VIS-NIR (400-1000nm)	N-BK7	#33-361	₹3,815 Volume Pricing	20+ In Stock
25.00	250.00	248.02	VIS-NIR (400-1000nm)	N-BK7	#67-182	₹3,815 Volume Pricing	Contact Us
25.00	300.00	298.02	VIS-NIR (400-1000nm)	N-BK7	#67-183	₹3,815 Volume Pricing	20+ In Stock
25.00	400.00	397.89	VIS-NIR (400-1000nm)	N-BK7	#33-367	₹3,815 Volume Pricing	7 In Stock
25.00	500.00	497.89	VIS-NIR (400-1000nm)	N-BK7	#47-387	₹3,815 Volume Pricing	7 In Stock
25.00	750.00	747.89	VIS-NIR (400-1000nm)	N-BK7	#47-388	₹3,815 Volume Pricing	5 In Stock
25.40	25.40	21.48	VIS-NIR (400-1000nm)	N-SF11	#62-599	₹3,970 Volume Pricing	20+ In Stock
25.40	38.10	33.48	VIS-NIR (400-1000nm)	N-BK7	#62-600	₹3,970 Volume Pricing	11 In Stock
25.40	50.80	47.50	VIS-NIR (400-1000nm)	N-BK7	#62-601	₹3,815 Volume Pricing	7 In Stock
25.40	63.50	60.37	VIS-NIR (400-1000nm)	N-BK7	#62-602	₹3,815 Volume Pricing	8 In Stock
25.40	76.20	73.56	VIS-NIR (400-1000nm)	N-BK7	#62-603	₹3,815 Volume Pricing	5 In Stock
25.40	88.90	86.26	VIS-NIR (400-1000nm)	N-BK7	#62-604	₹3,815 Volume Pricing	9 In Stock
25.40	101.60	98.97	VIS-NIR (400-1000nm)	N-BK7	#62-605	₹3,815 Volume Pricing	5 In Stock
30.00	30.00	26.13	VIS-NIR (400-1000nm)	N-SF11	#48-662	₹4,593 Volume Pricing	20+ In Stock

30.00	40.00	37.20	VIS-NIR (400-1000nm)	N-SF11	#67-184	₹4,437 Volume Pricing	6 In Stock
30.00	50.00	46.17	VIS-NIR (400-1000nm)	N-SF5	#45-709	₹4,437 Volume Pricing	20+ In Stock
30.00	60.00	56.03	VIS-NIR (400-1000nm)	N-BK7	#47-389	₹4,321 Volume Pricing	20+ In Stock
30.00	75.00	70.95	VIS-NIR (400-1000nm)	N-BK7	#45-710	₹4,321 Volume Pricing	2 In Stock
30.00	100.00	96.01	VIS-NIR (400-1000nm)	N-BK7	#45-711	₹4,321 Volume Pricing	1 In Stock
30.00	120.00	116.04	VIS-NIR (400-1000nm)	N-BK7	#47-390	₹4,321 Volume Pricing	20+ In Stock
40.00	40.00	35.13	VIS-NIR (400-1000nm)	N-SF11	#48-663	₹5,411 Volume Pricing	20+ In Stock
40.00	60.00	53.90	VIS-NIR (400-1000nm)	N-BK7	#45-712	₹5,411 Volume Pricing	14 In Stock
40.00	80.00	74.73	VIS-NIR (400-1000nm)	N-BK7	#33-385	₹5,333 Volume Pricing	8 In Stock
40.00	100.00	95.39	VIS-NIR (400-1000nm)	N-BK7	#33-373	₹5,333 Volume Pricing	5 In Stock
40.00	200.00	196.7	VIS-NIR (400-1000nm)	N-BK7	#33-379	₹5,333 Volume Pricing	Contact Us
40.00	300.00	296.70	VIS-NIR (400-1000nm)	N-BK7	#47-391	₹5,333 Volume Pricing	2 In Stock
40.00	400.00	396.70	VIS-NIR (400-1000nm)	N-BK7	#47-392	₹5,333 Volume Pricing	1 In Stock
50.00	50.00	43.28	VIS-NIR (400-1000nm)	N-SF11	#45-715	₹5,800 Volume Pricing	6 In Stock

50.00	75.00	67.75	VIS-NIR (400-1000nm)	N-BK7	#45-716	₹5,644 Volume Pricing	8 In Stock
50.00	100.00	93.41	VIS-NIR (400-1000nm)	N-BK7	#45-717	₹5,450 Volume Pricing	20+ In Stock
50.00	125.00	118.39	VIS-NIR (400-1000nm)	N-BK7	#47-393	₹5,450 Volume Pricing	20+ In Stock
50.00	150.00	144.07	VIS-NIR (400-1000nm)	N-BK7	#45-718	₹5,450 Volume Pricing	5 In Stock
50.00	175.00	169.05	VIS-NIR (400-1000nm)	N-BK7	#47-394	₹5,450 Volume Pricing	5 In Stock
50.00	200.00	196.66	VIS-NIR (400-1000nm)	N-BK7	#47-395	₹5,450 Volume Pricing	Contact Us
50.00	250.00	246.74	VIS-NIR (400-1000nm)	N-BK7	#47-396	₹5,450 Volume Pricing	6 In Stock
50.00	500.00	496.70	VIS-NIR (400-1000nm)	N-BK7	#47-397	₹5,450 Volume Pricing	1 In Stock
50.80	50.81	44.08	VIS-NIR (400-1000nm)	N-SF11	#71-340	₹5,800 Volume Pricing	2 In Stock
50.80	76.20	68.95	VIS-NIR (400-1000nm)	N-BK7	#71-347	₹5,644 Volume Pricing	1 In Stock
75.00	75.00	53.49	VIS-NIR (400-1000nm)	N-BK7	#86-911	₹11,288 Volume Pricing	1 In Stock
75.00	150.00	142.45	VIS-NIR (400-1000nm)	N-BK7	#86-912	₹11,133 Volume Pricing	2 In Stock
75.00	200.00	194.24	VIS-NIR (400-1000nm)	N-BK7	#86-913	₹11,133 Volume Pricing	10 In Stock
75.00	250.00	244.73	VIS-NIR (400-1000nm)	N-BK7	#86-914	₹11,133 Volume Pricing	5 In Stock

75.00	500.00	494.73	VIS-NIR (400-1000nm)	N-BK7	#86-915	₹11,133 Volume Pricing	Contact Us
10.00	12.50	10.99	VIS-NIR (400-1000nm)	N-SF11	#38-489	₹3,348 Volume Pricing	1 In Stock
10.00	17.50	15.66	VIS-NIR (400-1000nm)	N-BK7	#38-492	₹3,270 Volume Pricing	3 In Stock
12.00	25.00	23.22	VIS-NIR (400-1000nm)	N-BK7	#38-494	₹3,542 Volume Pricing	3 In Stock
12.00	50.00	48.75	VIS-NIR (400-1000nm)	N-BK7	#38-496	₹3,542 Volume Pricing	5 In Stock
12.50	12.50	10.40	VIS-NIR (400-1000nm)	N-SF11	#38-499	₹3,542 Volume Pricing	2 In Stock
12.50	15.00	13.26	VIS-NIR (400-1000nm)	N-SF11	#38-500	₹3,542 Volume Pricing	13 In Stock
12.50	20.00	17.69	VIS-NIR (400-1000nm)	N-BK7	#38-503	₹3,542 Volume Pricing	6 In Stock
12.50	25.00	22.96	VIS-NIR (400-1000nm)	N-BK7	#38-504	₹3,464 Volume Pricing	Contact Us
12.50	30.00	28.22	VIS-NIR (400-1000nm)	N-BK7	#38-505	₹3,464 Volume Pricing	7 In Stock
12.50	40.00	38.55	VIS-NIR (400-1000nm)	N-BK7	#38-507	₹3,464 Volume Pricing	5 In Stock
12.50	45.00	43.68	VIS-NIR (400-1000nm)	N-BK7	#38-508	₹3,464 Volume Pricing	1 In Stock
12.50	50.00	48.68	VIS-NIR (400-1000nm)	N-BK7	#38-509	₹3,464 Volume Pricing	17 In Stock
12.50	75.00	73.88	VIS-NIR (400-1000nm)	N-BK7	#38-510	₹3,464 Volume Pricing	1 In Stock

12.50	100.00	98.95	VIS-NIR (400-1000nm)	N-BK7	#38-512	₹3,464 Volume Pricing	5 In Stock
12.70	100.00	98.88	VIS-NIR (400-1000nm)	N-BK7	#38-518	₹3,464 Volume Pricing	6 In Stock
15.00	25.00	22.50	VIS-NIR (400-1000nm)	N-BK7	#38-519	₹3,542 Volume Pricing	3 In Stock
15.00	50.00	48.35	VIS-NIR (400-1000nm)	N-BK7	#38-520	₹3,542 Volume Pricing	4 In Stock
18.00	20.00	17.59	VIS-NIR (400-1000nm)	N-SF11	#38-521	₹3,698 Volume Pricing	4 In Stock
18.00	25.00	21.51	VIS-NIR (400-1000nm)	N-BK7	#38-522	₹3,698 Volume Pricing	1 In Stock
18.00	30.00	27.10	VIS-NIR (400-1000nm)	N-BK7	#38-523	₹3,581 Volume Pricing	8 In Stock
18.00	50.00	48.09	VIS-NIR (400-1000nm)	N-BK7	#38-524	₹3,581 Volume Pricing	5 In Stock
25.40	35.00	30.46	VIS-NIR (400-1000nm)	N-BK7	#38-525	₹3,970 Volume Pricing	1 In Stock
25.40	40.00	36.11	VIS-NIR (400-1000nm)	N-BK7	#38-542	₹3,970 Volume Pricing	Contact Us
25.40	75.00	72.69	VIS-NIR (400-1000nm)	N-BK7	#38-543	₹3,815 Volume Pricing	3 In Stock
25.40	100.00	98.02	VIS-NIR (400-1000nm)	N-BK7	#38-544	₹3,815 Volume Pricing	8 In Stock
25.40	125.00	123.02	VIS-NIR (400-1000nm)	N-BK7	#38-545	₹3,815 Volume Pricing	1 In Stock
25.40	150.00	148.02	VIS-NIR (400-1000nm)	N-BK7	#38-547	₹3,815 Volume Pricing	1 In Stock

35.00	35.00	30.52	VIS-NIR (400-1000nm)	N-SF11	#38-548	₹4,710 Volume Pricing	Contact Us
35.00	50.00	44.40	VIS-NIR (400-1000nm)	N-BK7	#38-552	₹4,593 Volume Pricing	2 In Stock
35.00	70.00	66.04	VIS-NIR (400-1000nm)	N-BK7	#38-561	₹4,593 Volume Pricing	5 In Stock
35.00	100.00	97.03	VIS-NIR (400-1000nm)	N-BK7	#38-567	₹4,593 Volume Pricing	14 In Stock
75.00	100.00	87.57	VIS-NIR (400-1000nm)	N-BK7	#71-870	₹11,133 Volume Pricing	3 In Stock
75.00	125.00	115.99	VIS-NIR (400-1000nm)	N-BK7	#71-871	₹11,133 Volume Pricing	7 In Stock
75.00	175.00	168.68	VIS-NIR (400-1000nm)	N-BK7	#71-872	₹11,133 Volume Pricing	1 In Stock
75.00	300.00	294.4	VIS-NIR (400-1000nm)	N-BK7	#71-873	₹11,133 Volume Pricing	2 In Stock
75.00	400.00	394.4	VIS-NIR (400-1000nm)	N-BK7	#71-874	₹11,133 Volume Pricing	3 In Stock
75.00	750.00	745.35	VIS-NIR (400-1000nm)	N-BK7	#71-875	₹11,133 Volume Pricing	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com