¾" Dia Stainless Posts, Vertical Post 15"

Stock **#39-352** **1 In Stock**

- 1 +

₹6,381

ADD TO CART

Volume Pricing	
Qty 1+	**₹6,381** each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:	Mounting Post

Physical & Mechanical Properties

Length (mm):	381.0

Weight (lbs):	1.50
Length (inches):	15.0
Diameter (inches):	3/4

Threading & Mounting

Mounting Threads:	3/4-16 Male (One End)

Regulatory Compliance

RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 250:	Compliant

PRODUCT DETAILS

- Posts for Integration into Imaging Systems
- Vertical Posts Thread to Bases and Platforms
- Horizontal Arms Thread to Posts and Microscope Head Mounts
- **Rack and Pinion Focusing Mounts**, and **Accessories** also Available

Stainless Steel Posts for Imaging Systems are used for constructing and supporting imaging systems. Vertical posts can be threaded directly into bases or platforms and include a steel collar with a set screw. Horizontal arms can be used with a 90° angle mount, on vertical posts, or with a breadboard adapter. Stainless Steel Posts for Imaging Systems are ¾ of an inch in diameter and are offered in lengths ranging from 9.0 inches (228.6mm) to 24.0 inches (609.6mm). The mounting threads for these posts are available threaded on one end with ¾"-16 male or threaded on both ends with a combination of ¼"-20 and 5/16"-18 pins.