

[All Products](#) / [Imaging Lenses](#) / [M12 Lenses \(S-Mount Lenses\)](#)

## TECHSPEC® Green Series M12 Lenses



- Up to 1/2", S-Mount Lens
- Up to 0.4 MegaPixels, 8.3µm Pixel Size Sensors
- Board Camera Lens Optimized for Close WD and Finite Conjugate
- 6mm to 25mm Focal Lengths

### Common Specifications

#### General

<b>Product Family:</b>	Green Series	<b>IR Cut Filter:</b>	No
<b>Imaging Lens Type:</b>	Standard Lens		

#### Physical & Mechanical Properties

<b>Iris Option:</b>	Fixed
---------------------	-------

#### Optical Properties

<b>Wavelength Range (nm):</b>	400 - 700	<b>Working Distance (mm):</b>	150 - ∞
<b>Coating Specification:</b>	λ/4 MgF <sub>2</sub> @ 580nm		


#### Sensor

<b>Pixel Size (µm):</b>	8.30
-------------------------	------

#### Threading & Mounting

<b>Filter Thread:</b>	N/A
-----------------------	-----

## Technical Information



## Products

Focal Length FL (mm)	Aperture (f/#)	Max. Sensor Format	Working Distance (mm)	IR Cut Filter	Stock Number	Price	Buy
6.00	f/1.9	1/3"	150 - ∞	No	<a href="#">#87-231</a>	₹8,648 <a href="#">Volume Pricing</a>	1 In Stock
6.00	f/4	1/3"	150 - ∞	No	<a href="#">#69-256</a>	₹8,344 <a href="#">Volume Pricing</a>	9 In Stock
6.00	f/5.6	1/3"	150 - ∞	No	<a href="#">#83-934</a>	₹8,344 <a href="#">Volume Pricing</a>	2 In Stock
6.00	f/8	1/3"	150 - ∞	No	<a href="#">#83-945</a>	₹8,344 <a href="#">Volume Pricing</a>	1 In Stock
8.00	f/1.9	1/3"	150 - ∞	No	<a href="#">#54-853</a>	₹8,648 <a href="#">Volume Pricing</a>	3 In Stock
12.00	f/2	1/2"	150 - ∞	No	<a href="#">#54-854</a>	₹8,648 <a href="#">Volume Pricing</a>	1 In Stock
25.00	f/2.1	1/2"	150 - ∞	No	<a href="#">#54-855</a>	₹8,648 <a href="#">Volume Pricing</a>	20+ In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)