

[All Products](#) / [Optics](#) / [Prisms](#) / [Retroreflection Prisms](#)

Hollow Retroreflectors



- Incident Light is Reflected Back to the Source
- Hollow Lightweight Design
- No Material Absorption or Chromatic Aberration

Common Specifications

Physical & Mechanical Properties

Dimensional Tolerance (mm):	±1.6
-----------------------------	------

Optical Properties

Substrate:	BOROFLOAT®		
Surface Quality:	80-50	Image Orientation:	Left-Handed
Ray Deviation (°):	180		

Technical Information

Products

CA (mm)	Beam Deviation (arcsec)	Coating	Stock Number	Price	Buy
6.4	20.00	Enhanced Aluminum (450- 650nm)	#46-169	₹1,04,708	10 to 12 days
6.4	20.00	Protected Gold (700- 2000nm)	#46-180	₹1,06,655	10 to 12 days
12.7	5.00	Enhanced Aluminum (450- 650nm)	#46-170	₹1,08,601	10 to 12 days
12.7	5.00	Protected Gold (700- 2000nm)	#46-181	₹1,09,769	10 to 12 days
25.4	1.00	Enhanced Aluminum (450- 650nm)	#46-172	₹1,08,601	10 to 12 days
25.4	1.00	Protected Gold (700- 2000nm)	#46-183	₹1,09,769	10 to 12 days
25.4	1.00	Protected Silver (450- 10000nm)	#70-688	₹1,09,769	10 to 12 days
25.4	2.00	Enhanced Aluminum (450- 650nm)	#46-173	₹82,910	10 to 12 days
25.4	2.00	Protected Gold (700- 2000nm)	#46-184	₹83,689	10 to 12 days
25.4	5.00	Enhanced Aluminum (450- 650nm)	#46-174	₹61,502	10 to 12 days

25.4	5.00	Protected Gold (700-2000nm)	#46-185	₹62,669	10 to 12 days
25.4	5.00	Protected Silver (450-10000nm)	#70-689	₹62,669	10 to 12 days
25.4	30.00	Enhanced Aluminum (450-650nm)	#46-175	₹50,213	10 to 12 days
25.4	30.00	Protected Gold (700-2000nm)	#46-186	₹52,160	10 to 12 days
50.8	1.00	Enhanced Aluminum (450-650nm)	#49-666	₹1,33,513	10 to 12 days
50.8	1.00	Protected Gold (700-2000nm)	#49-674	₹1,35,459	10 to 12 days
50.8	1.00	Protected Silver (450-10000nm)	#70-690	₹1,35,459	10 to 12 days
50.8	2.00	Enhanced Aluminum (450-650nm)	#49-667	₹1,09,379	10 to 12 days
50.8	2.00	Protected Gold (700-2000nm)	#49-675	₹1,11,326	10 to 12 days
50.8	5.00	Enhanced Aluminum (450-650nm)	#49-668	₹84,078	10 to 12 days
50.8	5.00	Protected Gold (700-2000nm)	#49-676	₹85,635	Contact Us
50.8	5.00	Protected Silver (450-10000nm)	#70-691	₹85,635	10 to 12 days

50.8	30.00	Enhanced Aluminum (450-650nm)	#49-669	₹63,837	10 to 12 days
50.8	30.00	Protected Gold (700-2000nm)	#49-677	₹66,173	10 to 12 days
63.5	1.00	Enhanced Aluminum (450-650nm)	#46-176	₹1,40,519	Contact Us
63.5	1.00	Protected Gold (700-2000nm)	#46-187	₹1,43,633	10 to 12 days
63.5	1.00	Protected Silver (450-10000nm)	#70-692	₹1,43,633	10 to 12 days
63.5	2.00	Enhanced Aluminum (450-650nm)	#46-177	₹1,15,607	10 to 12 days
63.5	2.00	Protected Gold (700-2000nm)	#46-188	₹1,18,332	10 to 12 days
63.5	5.00	Enhanced Aluminum (450-650nm)	#46-178	₹97,313	10 to 12 days
63.5	5.00	Protected Gold (700-2000nm)	#46-189	₹99,648	10 to 12 days
63.5	5.00	Protected Silver (450-10000nm)	#70-693	₹99,648	Contact Us

[#46-179 Clearance](#)



Clearance

63.5	30.00	Enhanced Aluminum (450-650nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹76,293	10 to 12 days
63.5	30.00	Protected Gold (700-2000nm)	#46-190	₹79,018	10 to 12 days
127.0	1.00	Enhanced Aluminum (450-650nm)	#49-670	₹8,22,096	Contact Us
127.0	1.00	Protected Gold (700-2000nm)	#49-678	₹8,26,767	Contact Us
127.0	1.00	Protected Silver (450-10000nm)	#70-694	₹8,26,767	10 to 12 days
127.0	5.00	Enhanced Aluminum (450-650nm)	#49-672	₹3,21,131	Contact Us
127.0	5.00	Protected Gold (700-2000nm)	#49-680	₹3,26,192	10 to 12 days
127.0	5.00	Protected Silver (450-10000nm)	#70-695	₹3,26,192	Contact Us
127.0	30.00	Protected Gold (700-2000nm)	#49-681	₹2,26,154	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com