


[All Products](#) / [Optics](#) / [Optical Filters](#) / [Neutral Density \(ND\) Filters](#)

Hoya Absorptive Neutral Density (ND) Filters See More by [Hoya](#)




- Attenuates Visible Light Via Absorption, Rather than Reflection
- Multiple Filters Can be Stacked for Increased Blocking
- Optical Densities from 0.1 to 4.0 are Available
- Also Available [Pre-mounted in C-Mount Housings](#)

Common Specifications

Physical & Mechanical Properties			
Thickness Tolerance (mm):		±0.5	
			Parallelism (mm): <0.02
Optical Properties			
Substrate:		ND Filter Glass	
			Coating: Uncoated
Surface Quality:		80-50	
			Blocking Wavelength Range (nm): 400 - 700

Technical Information



Products

Dia. (mm)	Dimensions (mm)	Glass/Filter Number	Optical Density OD (Average)	Thickness (mm)	Transmission (%)	Stock Number	Price	Buy
12.50	-	Hoya ND70	0.1	1.20	79.0	#63-456	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND70	0.1	1.20	79.0	#63-460	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND70	0.1	1.20	79.0	#63-464	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND70	0.1	1.20	79.0	#65-808	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND70	0.15	2.50	70.0	#48-523	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND70	0.15	2.50	70.0	#46-211	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND70	0.15	2.50	70.0	#46-217	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND70	0.15	2.50	70.0	#65-809	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND50	0.2	1.50	63.0	#63-457	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND50	0.2	1.50	63.0	#63-461	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND50	0.2	1.50	63.0	#63-465	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND50	0.2	1.50	63.0	#65-810	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND50	0.3	2.50	50.0	#48-524	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND50	0.3	2.50	50.0	#46-212	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND50	0.3	2.50	50.0	#46-218	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND50	0.3	2.50	50.0	#65-811	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND40	0.4	2.50	40.0	#48-525	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND40	0.4	2.50	40.0	#46-213	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND40	0.4	2.50	40.0	#46-219	₹7,629 Qty 11+ ₹6,773	10 to 12 days

50.00	-	Hoya ND40	0.4	2.50	40.0	#65-812	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND25	0.5	2.00	32.0	#48-526	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND25	0.5	2.00	32.0	#48-089	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND25	0.5	2.00	32.0	#48-094	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND25	0.5	2.00	32.0	#65-813	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND25	0.6	2.50	25.0	#48-527	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND25	0.6	2.50	25.0	#46-214	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND25	0.6	2.50	25.0	#46-220	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND25	0.6	2.50	25.0	#65-814	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND25	0.7	3.10	20.0	#63-458	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND25	0.7	3.10	20.0	#63-462	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND25	0.7	3.10	20.0	#63-466	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND25	0.7	3.10	20.0	#65-815	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND13	0.9	2.50	12.5	#48-528	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND13	0.9	2.50	12.5	#46-215	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND13	0.9	2.50	12.5	#46-221	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND13	0.9	2.50	12.5	#65-816	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND0.3	1.0	1.00	10.0	#48-529	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND0.3	1.0	1.00	10.0	#48-090	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND0.3	1.0	1.00	10.0	#48-095	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND0.3	1.0	1.00	10.0	#65-817	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND0.3	1.3	1.45	5.0	#63-459	₹2,491 Qty 11+ ₹2,258	10 to 12 days

25.00	-	Hoya ND0.3	1.3	1.45	5.0	#63-463	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND0.3	1.3	1.45	5.0	#63-467	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND0.3	1.3	1.45	5.0	#65-818	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND0.3	1.5	1.50	3.0	#48-530	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND0.3	1.5	1.50	3.0	#48-091	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND0.3	1.5	1.50	3.0	#48-096	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND0.3	1.5	1.50	3.2	#65-819	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND0.3	2.0	2.00	1.0	#48-531	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND0.3	2.0	2.00	1.0	#48-092	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND0.3	2.0	2.00	1.0	#48-097	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND0.3	2.0	2.00	1.0	#65-820	₹7,629 Qty 11+ ₹6,773	7 days
12.50	-	Hoya ND0.3	2.5	2.50	0.3	#48-532	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND0.3	2.5	2.50	0.3	#46-216	₹3,581 Qty 11+ ₹3,192	Contact Us
-	50.0 x 50.0	Hoya ND0.3	2.5	2.50	0.3	#46-222	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND0.3	2.5	2.50	0.3	#65-821	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND0.3	3.0	3.00	0.1	#48-533	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND0.3	3.0	3.00	0.1	#48-093	₹3,581 Qty 11+ ₹3,192	10 to 12 days
-	50.0 x 50.0	Hoya ND0.3	3.0	3.00	0.1	#48-098	₹7,629 Qty 11+ ₹6,773	10 to 12 days
50.00	-	Hoya ND0.3	3.0	3.00	0.1	#65-822	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND006	3.5	2.50	0.03	#36-268	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND006	3.5	2.50	0.03	#36-269	₹3,581 Qty 11+ ₹3,192	10 to 12 days
50.00	-	Hoya ND006	3.5	2.50	0.03	#36-270	₹7,629 Qty 11+ ₹6,773	10 to 12 days

-	50.0 x 50.0	Hoya ND006	3.5	2.50	0.03	#36-271	₹7,629 Qty 11+ ₹6,773	10 to 12 days
12.50	-	Hoya ND006	4.00	2.85	0.01	#36-272	₹2,491 Qty 11+ ₹2,258	10 to 12 days
25.00	-	Hoya ND006	4.00	2.85	0.01	#36-273	₹3,581 Qty 11+ ₹3,192	10 to 12 days
50.00	-	Hoya ND006	4.00	2.85	0.01	#36-276	₹7,629 Qty 11+ ₹6,773	10 to 12 days
-	50.0 x 50.0	Hoya ND006	4.00	2.85	0.01	#36-277	₹7,629 Qty 11+ ₹6,773	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com