


[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Visible Windows](#)

# High Efficiency Anti-Reflection (HEAR) Coated Windows



- High Transmission
- Eliminate Back Reflections and Reduce Glare
- Available in a Wide Range of Sizes

## Common Specifications


### Physical & Mechanical Properties

<b>Bevel:</b>	Protective as needed	<b>Clear Aperture (%):</b>	≥90
---------------	----------------------	----------------------------	-----



### Optical Properties

<b>Angle of Incidence (°):</b>	0	<b>Coating:</b>	BBAR (425-700nm)
<b>Coating Specification:</b>	$R_{avg} \leq 0.5\% @ 425 - 700nm$	<b>Substrate:</b>	Float Glass
<b>Surface Quality:</b>	80-50	<b>Wavelength Range (nm):</b>	425 - 700

# Technical Information



Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
<a href="#">#71-564 New</a>						
						
New						
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!						
5.00	-	1.00	BBAR (425-700nm)		₹1,479 Qty 6+ ₹1,183	10 to 12 days
<a href="#">#71-565 New</a>						
						
New						
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!						
5.00	-	3.00	BBAR (425-700nm)		₹1,479 Qty 6+ ₹1,183	10 to 12 days

[#71-566 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

10.00	-	1.00	BBAR (425-700nm)		₹1,590 Qty 6+ ₹1,272	10 to 12 days
-------	---	------	------------------	--	-------------------------	---------------

---

[#71-567 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

10.00	-	3.00	BBAR (425-700nm)		₹1,590 Qty 6+ ₹1,272	10 to 12 days
-------	---	------	------------------	--	-------------------------	---------------

---

12.50	-	1.00	BBAR (425-700nm)	<a href="#">#21-324</a>	₹1,632 Qty 6+ ₹1,320	Contact Us
-------	---	------	------------------	-------------------------	-------------------------	------------

---

12.70	-	1.00	BBAR (425-700nm)	<a href="#">#39-279</a>	₹1,632 Qty 6+ ₹1,320	10 to 12 days
-------	---	------	------------------	-------------------------	-------------------------	---------------

---

[#71-590 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

12.70

-

2.00

BBAR  
(425-700nm)

₹1,632  
Qty 6+ ₹1,320

10 to 12 days

12.70

-

3.00

BBAR  
(425-700nm)

[#39-283](#)

₹1,632  
Qty 6+ ₹1,320

10 to 12 days

[#71-582 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-

12.70 x 12.70

1.00

BBAR  
(425-700nm)

₹1,664  
Qty 6+ ₹1,331

10 to 12 days

[#71-583 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	12.70 x 12.70	3.00	BBAR (425-700nm)	₹1,664 Qty 6+ ₹1,331	10 to 12 days
---	---------------	------	------------------	-------------------------	---------------

---

[#71-568 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

15.00	-	1.00	BBAR (425-700nm)	₹1,645 Qty 6+ ₹1,316	10 to 12 days
-------	---	------	------------------	-------------------------	---------------

---

[#71-569 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

15.00

-

3.00

BBAR  
(425-  
700nm)

₹1,645  
Qty 6+ ₹1,316

10 to 12 days

---

[#71-570 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

20.00

-

1.00

BBAR  
(425-  
700nm)

₹1,645  
Qty 6+ ₹1,316

10 to 12 days

---

[#71-571 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

20.00	-	3.00	BBAR (425- 700nm)		₹1,645 Qty 6+ ₹1,316	10 to 12 days
25.00	-	1.00	BBAR (425- 700nm)	<a href="#">#21-325</a>	₹1,632 Qty 6+ ₹1,320	10 to 12 days
25.40	-	1.00	BBAR (425- 700nm)	<a href="#">#48-924</a>	₹1,632 Qty 6+ ₹1,320	10 to 12 days
-	25.40 x 25.40	1.00	BBAR (425- 700nm)	<a href="#">#48-923</a>	₹1,632 Qty 6+ ₹1,320	10 to 12 days



[#71-591 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

25.40	-	2.00	BBAR (425- 700nm)		₹1,632 Qty 6+ ₹1,320	10 to 12 days
-------	---	------	-------------------------	--	-------------------------	---------------

---

25.40	-	3.00	BBAR (425- 700nm)	<a href="#">#46-098</a>	₹1,632 Qty 6+ ₹1,320	10 to 12 days
-------	---	------	-------------------------	-------------------------	-------------------------	---------------

---

-	25.40 x 25.40	3.00	BBAR (425- 700nm)	<a href="#">#46-097</a>	₹1,632 Qty 6+ ₹1,320	10 to 12 days
---	---------------	------	-------------------------	-------------------------	-------------------------	---------------

---

[#71-584 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

-	25.40 x 50.80	1.00	BBAR (425- 700nm)		₹1,738 Qty 6+ ₹1,390	10 to 12 days
---	---------------	------	-------------------------	--	-------------------------	---------------

---

[#71-585 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	25.40 x 50.80	3.00	BBAR (425-700nm)	₹1,738 Qty 6+ ₹1,390	10 to 12 days
---	---------------	------	------------------	-------------------------	---------------

---

[#71-572 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

30.00	-	1.00	BBAR (425-700nm)	₹1,738 Qty 6+ ₹1,390	10 to 12 days
-------	---	------	------------------	-------------------------	---------------

---

[#71-573 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

30.00

-

3.00

BBAR  
(425-700nm)

₹1,738  
Qty 6+ ₹1,390

10 to 12 days

---

[#71-574 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

35.00

-

1.00

BBAR  
(425-700nm)

₹1,738  
Qty 6+ ₹1,390

10 to 12 days

---

[#71-575 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

35.00

-

3.00

BBAR  
(425-700nm)

₹1,738  
Qty 6+ ₹1,390

10 to 12 days

38.10

-

1.00

BBAR  
(425-700nm)

[#39-280](#)

₹1,724  
Qty 6+ ₹1,375

10 to 12 days

[#71-592 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

38.10

-

2.00

BBAR  
(425-700nm)

₹1,724  
Qty 6+ ₹1,375

10 to 12 days

38.10

-

3.00

BBAR  
(425-700nm)

[#39-284](#)

₹1,724  
Qty 6+ ₹1,375

10 to 12 days

[#71-576 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

40.00

-

1.00

BBAR  
(425-  
700nm)

₹1,738  
Qty 6+ ₹1,390

10 to 12 days

---

[#71-577 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

40.00

-

3.00

BBAR  
(425-  
700nm)

₹1,738  
Qty 6+ ₹1,390

10 to 12 days

---

50.00

-

3.00

BBAR  
(425-  
700nm)

[#21-326](#)

₹1,724  
Qty 6+ ₹1,375

10 to 12 days

---

50.80

-

1.00

BBAR  
(425-  
700nm)

[#48-926](#)

₹1,724  
Qty 6+ ₹1,375

10 to 12 days

---

- 50.80 x 50.80

1.00

BBAR  
(425-  
700nm)

[#48-925](#)

₹1,724  
Qty 6+ ₹1,375

10 to 12 days

---

[#71-593 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

50.80	-	2.00	BBAR (425-700nm)		₹1,724 Qty 6+ ₹1,375	10 to 12 days
-------	---	------	------------------	--	-------------------------	---------------

---

[#71-594 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	50.80 x 50.80	2.00	BBAR (425-700nm)		₹1,724 Qty 6+ ₹1,375	10 to 12 days
---	---------------	------	------------------	--	-------------------------	---------------

---

50.80	-	3.00	BBAR (425-700nm)	<a href="#">#46-100</a>	₹1,724 Qty 6+ ₹1,375	10 to 12 days
-------	---	------	------------------	-------------------------	-------------------------	---------------

---

-	50.80 x 50.80	3.00	BBAR (425-700nm)	<a href="#">#46-099</a>	₹1,724 Qty 6+ ₹1,375	10 to 12 days
---	---------------	------	------------------	-------------------------	-------------------------	---------------

---

[#71-586 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	50.80 x 76.20	1.00	BBAR (425-700nm)	₹2,237 Qty 6+ ₹1,790	10 to 12 days
---	---------------	------	------------------	-------------------------	---------------

---

[#71-587 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	50.80 x 76.20	3.00	BBAR (425-700nm)	₹2,237 Qty 6+ ₹1,790	10 to 12 days
---	---------------	------	------------------	-------------------------	---------------

---

63.50	-	1.00	BBAR (425-700nm)	<a href="#">#39-281</a> ₹1,944 Qty 6+ ₹1,559	10 to 12 days
-------	---	------	------------------	--	---------------

---

63.50	-	3.00	BBAR (425-700nm)	<a href="#">#39-285</a> ₹1,944 Qty 6+ ₹1,559	Contact Us
-------	---	------	------------------	--	------------

---

75.00	-	3.00	BBAR (425-700nm)	<a href="#">#21-328</a> ₹2,219 Qty 6+ ₹1,779	10 to 12 days
-------	---	------	------------------	--	---------------

---

76.20	-	1.00	BBAR (425-700nm)	<a href="#">#48-928</a>	₹2,219 Qty 6+ ₹1,779	10 to 12 days
-------	---	------	---------------------	-------------------------	-------------------------	---------------

-	76.20 x 76.20	1.00	BBAR (425-700nm)	<a href="#">#48-927</a>	₹2,219 Qty 6+ ₹1,779	10 to 12 days
---	---------------	------	---------------------	-------------------------	-------------------------	---------------

[#71-595 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

76.20	-	2.00	BBAR (425-700nm)		₹2,219 Qty 6+ ₹1,779	10 to 12 days
-------	---	------	---------------------	--	-------------------------	---------------

[#71-596 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-	76.20 x 76.20	2.00	BBAR (425-700nm)		₹2,219 Qty 6+ ₹1,779	10 to 12 days
---	---------------	------	---------------------	--	-------------------------	---------------



76.20	-	3.00	BBAR (425-700nm)	<a href="#">#46-102</a>	₹2,219 Qty 6+ ₹1,779	10 to 12 days
-	76.20 x 76.20	3.00	BBAR (425-700nm)	<a href="#">#46-101</a>	₹2,219 Qty 6+ ₹1,779	10 to 12 days
88.90	-	1.00	BBAR (425-700nm)	<a href="#">#39-282</a>	₹2,549 Qty 6+ ₹2,035	10 to 12 days
88.90	-	3.00	BBAR (425-700nm)	<a href="#">#39-286</a>	₹2,549 Qty 6+ ₹2,035	10 to 12 days
101.60	-	1.00	BBAR (425-700nm)	<a href="#">#48-930</a>	₹2,897 Qty 6+ ₹2,329	10 to 12 days
-	101.60 x 101.60	1.00	BBAR (425-700nm)	<a href="#">#48-929</a>	₹2,897 Qty 6+ ₹2,329	10 to 12 days

[#71-597 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

101.60	-	2.00	BBAR (425-700nm)		₹2,897 Qty 6+ ₹2,329	10 to 12 days
--------	---	------	---------------------	--	-------------------------	---------------

[#71-598 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

-	101.60 x 101.60	2.00	BBAR (425- 700nm)		₹2,897 Qty 6+ ₹2,329	10 to 12 days
---	--------------------	------	-------------------------	--	-------------------------	---------------

101.60	-	3.00	BBAR (425- 700nm)	<a href="#">#46-104</a>	₹2,897 Qty 6+ ₹2,329	10 to 12 days
--------	---	------	-------------------------	-------------------------	-------------------------	---------------

-	101.60 x 101.60	3.00	BBAR (425- 700nm)	<a href="#">#46-103</a>	₹2,897 Qty 6+ ₹2,329	Contact Us
---	--------------------	------	-------------------------	-------------------------	-------------------------	------------

-	101.60 x 127.00	3.00	BBAR (425- 700nm)	<a href="#">#21-329</a>	₹3,136 Qty 6+ ₹2,494	10 to 12 days
---	--------------------	------	-------------------------	-------------------------	-------------------------	---------------

127.00	-	1.00	BBAR (425- 700nm)	<a href="#">#63-216</a>	₹3,741 Qty 6+ ₹3,007	10 to 12 days
--------	---	------	-------------------------	-------------------------	-------------------------	---------------

-	127.00 x 177.80	1.00	BBAR (425- 700nm)	<a href="#">#63-217</a>	₹3,741 Qty 6+ ₹3,007	10 to 12 days
---	--------------------	------	-------------------------	-------------------------	-------------------------	---------------

[#71-599 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

127.00

-

2.00

BBAR  
(425-700nm)

₹3,741  
Qty 6+ ₹3,007

10 to 12 days

---

[#71-600 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

-

127.00 x  
177.80

2.00

BBAR  
(425-700nm)

₹3,741  
Qty 6+ ₹3,007

10 to 12 days

---

127.00

-

3.00

BBAR  
(425-700nm)

[#48-858](#)

₹3,741  
Qty 6+ ₹3,007

10 to 12 days

---

-

127.00 x  
177.80

3.00

BBAR  
(425-700nm)

[#43-973](#)

₹3,741  
Qty 6+ ₹3,007

10 to 12 days

---

[#71-578 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

152.00

-

1.00

BBAR  
(425-700nm)

₹4,067  
Qty 6+ ₹3,254

10 to 12 days

---

[#71-579 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

152.00

-

3.00

BBAR  
(425-700nm)

₹4,067  
Qty 6+ ₹3,254

10 to 12 days

---

[#71-580 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

177.00	-	1.00	BBAR (425-700nm)		₹4,252 Qty 6+ ₹3,402	10 to 12 days
--------	---	------	------------------	--	-------------------------	---------------

---

[#71-581 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

177.00	-	3.00	BBAR (425-700nm)		₹4,252 Qty 6+ ₹3,402	10 to 12 days
--------	---	------	------------------	--	-------------------------	---------------

---

203.20	-	1.00	BBAR (425-700nm)	<a href="#">#63-218</a>	₹4,584 Qty 6+ ₹3,668	10 to 12 days
--------	---	------	------------------	-------------------------	-------------------------	---------------

---

-	203.20 x 203.20	3.00	BBAR (425-700nm)	<a href="#">#21-330</a>	₹4,584 Qty 6+ ₹3,668	10 to 12 days
---	-----------------	------	------------------	-------------------------	-------------------------	---------------

---

-	203.20 x 254.00	1.00	BBAR (425- 700nm)	<a href="#">#63-219</a>	₹4,584 Qty 6+ ₹3,668	10 to 12 days
203.20	-	3.00	BBAR (425- 700nm)	<a href="#">#48-859</a>	₹4,584 Qty 6+ ₹3,668	10 to 12 days
-	203.20 x 254.00	3.00	BBAR (425- 700nm)	<a href="#">#43-974</a>	₹4,584 Qty 6+ ₹3,668	10 to 12 days
254.00	-	1.00	BBAR (425- 700nm)	<a href="#">#63-220</a>	₹6,675 Qty 6+ ₹5,355	10 to 12 days
-	254.00 x 254.00	3.00	BBAR (425- 700nm)	<a href="#">#21-331</a>	₹6,675 Qty 6+ ₹5,355	10 to 12 days
-	254.00 x 304.80	1.00	BBAR (425- 700nm)	<a href="#">#63-221</a>	₹6,675 Qty 6+ ₹5,355	10 to 12 days
254.00	-	3.00	BBAR (425- 700nm)	<a href="#">#48-860</a>	₹6,675 Qty 6+ ₹5,355	10 to 12 days
-	254.00 x 304.80	3.00	BBAR (425- 700nm)	<a href="#">#43-975</a>	₹6,675 Qty 6+ ₹5,355	10 to 12 days
-	304.80 x 304.80	3.00	BBAR (425- 700nm)	<a href="#">#21-332</a>	₹7,995 Qty 6+ ₹6,381	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)