

[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Iris Diaphragms](#)

High Performance Standard Series Iris Diaphragms



- Corrosion and High Temperature Resistance Housing
- Anti-Reflective (AR) Spring Steel or Burnished Spring Steel Leaf Options Available
- Mounted Version Features both an English and Metric Tapped Hole for Easy Post Mounting

Technical Information

Products

Type	Minimum Aperture (mm)	Maximum Aperture (mm)	Outer Diameter (mm)	Number of Leaves	Stock Number	Price	Buy
Unmounted	0.5, Typical	5.0	10.0	8.00	#57-573	₹7,775 Qty 5+ ₹6,866	10 to 12 days
Unmounted	0.5, Typical	7.0	12.0	8.00	#57-574	₹7,775 Qty 5+ ₹6,866	10 to 12 days
Unmounted	0.8, Typical	8	14.8	8	#64-507	₹5,281 Qty 5+ ₹4,658	10 to 12 days
Unmounted	1.0, Typical	12.0	19.8	11.00	#57-575	₹5,281 Qty 5+ ₹4,658	10 to 12 days
Unmounted	1.0, Typical	18.0	28.0	12.00	#57-576	₹5,281 Qty 5+ ₹4,658	10 to 12 days
Unmounted	1.2, Typical	20.0	30.0	12.00	#57-577	₹6,491 Qty 5+ ₹5,751	10 to 12 days
Unmounted	1.5, Typical	25.00	37.0	15.00	#84-131	₹6,491 Qty 5+ ₹5,751	10 to 12 days
Unmounted	0.5, Typical	5.0	10.0	8.00	#57-578	₹7,775 Qty 5+ ₹6,866	10 to 12 days
Unmounted	0.5, Typical	7.0	12.0	8.00	#57-579	₹7,775 Qty 5+ ₹6,866	10 to 12 days
Unmounted	1.0, Typical	8.0	14.8	9	#57-580	₹5,281 Qty 5+ ₹4,658	10 to 12 days
Unmounted	1.0, Typical	12.0	19.8	11.00	#57-581	₹5,281 Qty 5+ ₹4,658	Contact Us
Unmounted	1.2, Typical	20.0	30.0	12.00	#64-508	₹6,491 Qty 5+ ₹5,751	10 to 12 days
Unmounted	1.5, Typical	25.0	37.0	15.00	#57-582	₹6,491 Qty 5+ ₹5,751	10 to 12 days
Unmounted	2.5, Typical	37.0	53.0	16.00	#57-583	₹6,491 Qty 5+ ₹5,751	Contact Us
Unmounted	2.5, Typical	50.0	70.0	18.00	#57-584	₹13,423 Qty 5+ ₹11,875	10 to 12 days
Unmounted	4.0, Typical	60.0	82.0	17.00	#57-585	₹15,330 Qty 5+ ₹13,518	10 to 12 days

Unmounted	4.0, Typical	75.0	100.0	20.00	#57-586	₹23,032 Qty 5+ ₹20,303	10 to 12 days
Mounted	0.5, Typical	5.0	26.5	8.00	#23-255	₹8,949 Qty 5+ ₹7,885	10 to 12 days
Mounted	0.5, Typical	7.0	26.5	8.00	#23-256	₹8,949 Qty 5+ ₹7,885	10 to 12 days
Mounted	0.8, Typical	8.0	26.5	8.00	#23-257	₹6,491 Qty 5+ ₹5,721	10 to 12 days
Mounted	1.0, Typical	12.0	39.0	11.00	#23-258	₹6,491 Qty 5+ ₹5,721	10 to 12 days
Mounted	1.0, Typical	18.0	52.0	12.00	#23-259	₹6,491 Qty 5+ ₹5,721	10 to 12 days
Mounted	1.2, Typical	20.0	52.0	12.00	#23-260	₹7,628 Qty 5+ ₹6,719	10 to 12 days
Mounted	1.5, Typical	25.0	52.0	15.00	#23-261	₹7,628 Qty 5+ ₹6,719	10 to 12 days
Mounted	0.5, Typical	7.0	26.5	8.00	#23-262	₹8,949 Qty 5+ ₹7,885	10 to 12 days
Mounted	1.0, Typical	8.0	26.5	9.00	#23-263	₹6,491 Qty 5+ ₹5,721	10 to 12 days
Mounted	1.0, Typical	12.0	39.0	11.00	#23-264	₹6,491 Qty 5+ ₹5,721	10 to 12 days
Mounted	1.2, Typical	20.0	52.0	12.00	#23-265	₹7,628 Qty 5+ ₹6,719	10 to 12 days
Mounted	1.5, Typical	25.0	52.0	15.00	#23-266	₹7,628 Qty 5+ ₹6,719	10 to 12 days
Mounted	2.5, Typical	50.0	90.0	18.00	#23-267	₹14,303 Qty 5+ ₹12,594	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com