

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Specialty Lenses](#)

Gradient Index (GRIN) Rod Lenses




- Ideal for Fiber Coupling and Laser Diode Applications
- Comparable Performance to Conventional Aspherical Singlets
- Multiple Sizes and Wavelength Options
- [GRIN Lens Grippers and Table Mounts](#) Available

Common Specifications

Physical & Mechanical Properties			
Clear Aperture (%):		90.00	Length Tolerance (%): ±5
Optical Properties			
Substrate:		Aluminosilicate Glass Embedded with Silver Ions	Surface Quality: 40-20
Working Distance Tolerance (mm):		±0.02	

Technical Information



Products

Dia. (mm)	Substrate	Type	Coating	EFL (mm)	NA	Stock Number	Price	Buy
0.35	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.30	0.55	#88-355	₹7,560 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.45	0.54	#64-515	₹5,310 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.88	0.54	#64-517	₹5,310 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.67	0.52	#64-519	₹5,310 Volume Pricing	Contact Us
#64-520 Clearance								
								
Clearance								
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.71	0.52		₹5,310 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.45	0.53	#64-521	₹5,310 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.89	0.54	#64-523	₹5,310 Volume Pricing	20+ In Stock

1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.90	0.53	#64-524	₹5,310 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.68	0.52	#64-525	₹5,310 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.70	0.51	#64-526	₹5,310 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.46	0.52	#64-527	₹5,310 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.90	0.53	#64-529	₹5,310 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.71	0.51	#64-531	₹5,310 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	0.45	0.54	#64-533	₹6,300 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	0.88	0.54	#64-535	₹6,300 Volume Pricing	Contact Us
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	1.67	0.52	#64-537	₹6,300 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	1.69	0.52	#64-538	₹6,300 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	0.45	0.53	#64-539	₹6,300 Volume Pricing	8 In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	0.89	0.54	#64-541	₹6,300 Volume Pricing	20+ In Stock

1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	1.68	0.52	#64-543	₹6,300 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	1.70	0.51	#64-544	₹6,300 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	0.46	0.52	#64-545	₹6,300 Volume Pricing	11 In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	0.90	0.53	#64-547	₹6,300 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	1.71	0.51	#64-549	₹6,300 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	1.72	0.51	#64-550	₹6,300 Volume Pricing	20+ In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com