

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Bandpass Filters](#)

Infrared (IR) Bandpass Filters



- Ideal for Gas Analysis
- Center Wavelengths of 2.7-12.4μm
- Single Substrate Interference Filter

Common Specifications


Physical & Mechanical Properties

Thickness (mm):	1.00 ±0.2
-----------------	-----------

Optical Properties

Angle of Incidence (°):	0		
Optical Density OD (Average):	≥3.0	Coating:	Traditional Coated

Technical Information



Products

Dia. (mm)	CWL (nm)	FWHM (nm)	Stock Number	Price	Buy
25.00	2,700.00	110.00	#84-069	₹41,490 Qty 10+ ₹37,350	10 to 12 days
25.00	2,950.00	110.00	#84-070	₹41,490 Qty 10+ ₹37,350	10 to 12 days
25.00	3,460.00	140.00	#84-071	₹41,490 Qty 10+ ₹37,350	10 to 12 days
25.00	3,600.00	140.00	#84-072	₹41,490 Qty 10+ ₹37,350	10 to 12 days
12.50	4,000.00	2,000.00	#26-569	₹22,050 Qty 10+ ₹19,890	Contact Us
25.00	4,000.00	2,000.00	#11-998	₹41,490 Qty 10+ ₹37,350	10 to 12 days
50.00	4,000.00	2,000.00	#26-570	₹88,200 Qty 10+ ₹79,200	10 to 12 days
25.00	4,260.00	120.00	#84-073	₹41,490 Qty 10+ ₹37,350	Contact Us
25.00	4,670.00	150.00	#84-074	₹41,490 Qty 10+ ₹37,350	10 to 12 days
25.00	5,300.00	420.00	#84-075	₹41,490 Qty 10+ ₹37,350	10 to 12 days
25.00	6,000.00	500.00	#17-244	₹57,150 Qty 10+ ₹51,300	10 to 12 days
25.00	6,500.00	500.00	#17-245	₹57,150 Qty 10+ ₹51,300	10 to 12 days
25.00	7,000.00	500.00	#17-246	₹57,150 Qty 10+ ₹51,300	10 to 12 days

[#75-125 New](#)



New

25.00	7,500.00	500.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹55,245	10 to 12 days
25.00	8,000.00	500.00	#17-248	₹57,150 Qty 10+ ₹51,300	10 to 12 days
25.00	8,500.00	500.00	#70-192	₹57,150	10 to 12 days
25.00	9,000.00	500.00	#17-250	₹57,150 Qty 10+ ₹51,300	10 to 12 days
25.00	9,500.00	500.00	#17-251	₹57,150 Qty 10+ ₹51,300	10 to 12 days
25.00	10,000.00	500.00	#17-252	₹57,150 Qty 10+ ₹51,300	10 to 12 days
25.00	10,000.00	4,000.00	#11-999	₹78,300 Qty 10+ ₹70,650	10 to 12 days
12.50	10,600.00	1,500.00	#33-144	₹41,490 Qty 10+ ₹37,350	10 to 12 days
25.00	10,600.00	500.00	#25-720	₹57,150 Qty 10+ ₹51,300	10 to 12 days
25.00	10,600.00	1,500.00	#33-145	₹78,300 Qty 10+ ₹70,650	Contact Us
50.00	10,600.00	1,500.00	#33-146	₹1,93,500 Qty 10+ ₹1,74,150	10 to 12 days
25.00	11,100.00	500.00	#25-721	₹57,150 Qty 10+ ₹51,300	10 to 12 days
25.00	11,600.00	500.00	#25-722	₹57,150 Qty 10+ ₹51,300	10 to 12 days
25.00	12,100.00	500.00	#25-723	₹57,150 Qty 10+ ₹51,300	10 to 12 days

25.00 12,400.00 500.00

[#17-253](#)

₹78,300
Qty 10+ ₹70,650

[Contact Us](#)



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com