

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Machine Vision Lasers](#)

Coherent® StingRay™ and BioRay™ Laser Diode Modules

See More by [Coherent®](#)



- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available



Common Specifications

General

Manufacturer: Coherent®

Type of Laser: Diode

Optical Properties

Spatial Mode: TEM₀₀

Hardware & Interface Connectivity

Power Supply:

Power Supply Required and Sold Separately:

USA: [#86-878](#)

Europe: [#86-878](#)

Japan: [#86-878](#)

Korea: [#86-878](#)

China: [#86-878](#)

Output Type:

Free Space

Environmental & Durability Factors

Storage Temperature (°C):

-20 to +60

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Fan Angle (°)	Stock Number	Price	Buy
405.00	50	-	#89-373	₹2,54,700	7 days
450.00	50	-	#89-374	₹2,29,500	10 to 12 days
488.00	20	-	#89-375	₹4,28,850	10 to 12 days
520.00	50	-	#89-376	₹1,67,850	10 to 12 days
640.00	40	-	#89-377	₹1,01,250	10 to 12 days
520.00	5	-	#86-848	₹76,050	10 to 12 days
520.00	10	-	#87-522	₹85,950	Contact Us
640.00	5	-	#86-849	₹34,380	10 to 12 days
640.00	10	-	#87-523	₹46,350	10 to 12 days
640.00	35	-	#87-524	₹60,750	10 to 12 days
655.00	5	-	#86-850	₹34,380	Contact Us
655.00	10	-	#87-525	₹46,350	Contact Us
785.00	50	-	#87-527	₹60,750	Contact Us
785.00	90	-	#87-528	₹71,550	Contact Us
520.00	5	30.00	#86-851	₹99,000	10 to 12 days
520.00	5	45.00	#86-852	₹99,000	10 to 12 days

520.00	5	60.00	#86-853	₹99,000	Contact Us
520.00	35	30.00	#86-854	₹1,24,200	Contact Us
520.00	35	45.00	#86-855	₹1,24,200	10 to 12 days
520.00	35	60.00	#86-856	₹1,24,200	Contact Us
640.00	5	30.00	#86-857	₹61,200	10 to 12 days
640.00	5	45.00	#86-858	₹61,200	10 to 12 days
640.00	5	60.00	#86-859	₹61,200	10 to 12 days
640.00	35	30.00	#86-860	₹76,500	Contact Us
640.00	35	45.00	#86-861	₹76,500	10 to 12 days
640.00	35	60.00	#86-862	₹76,500	10 to 12 days
655.00	5	30.00	#86-863	₹56,700	10 to 12 days
655.00	5	45.00	#86-864	₹56,700	10 to 12 days
655.00	5	60.00	#86-865	₹61,200	10 to 12 days
660.00	35	30.00	#86-866	₹63,450	10 to 12 days
660.00	35	45.00	#86-867	₹63,450	Contact Us
660.00	35	60.00	#86-868	₹63,450	Contact Us
660.00	50	30.00	#86-869	₹72,000	10 to 12 days
660.00	50	45.00	#86-870	₹72,000	Contact Us
660.00	100	30.00	#33-287	₹1,10,700	Contact Us

660.00	50	60.00	#86-871	₹72,000	10 to 12 days
785.00	35	30.00	#86-872	₹69,750	Contact Us
785.00	35	45.00	#86-873	₹69,750	Contact Us
785.00	35	60.00	#86-874	₹69,750	Contact Us
785.00	50	30.00	#86-875	₹76,500	Contact Us
785.00	50	45.00	#86-876	₹69,750	Contact Us
785.00	50	60.00	#86-877	₹76,500	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com