

[All Products](#) / [Cameras](#) / [USB Cameras](#)

# Teledyne FLIR IIS Blackfly® USB 3.0 Cameras

 See More by [Teledyne FLIR](#)


- Ultra-Compact Design
- USB 3.0 Connectivity for Increased Image Transfer Rate
- Includes Image Capture Software and FlyCapture2 SDK
- [GigE](#) Versions Also Available



## Common Specifications

### General

<b>Manufacturer:</b>	FLIR	<b>Camera Series:</b>	Blackfly®
----------------------	------	-----------------------	-----------

### Physical & Mechanical Properties

<b>Dimensions (mm):</b>	29 x 29 x 30 (excludes connectors and lens mount)	<b>Weight (g):</b>	36
<b>Housing:</b>	Full		

### Sensor

<b>Image Buffer:</b>	16MB
----------------------	------

<b>Sensor Format:</b>	1/1.2"	<b>Resolution (Megapixels):</b>	2.30
<b>Frame Rate (fps):</b>	41.00	<b>Pixels (H x V):</b>	1,920 x 1,200
<b>Pixel Size, H x V (µm):</b>	5.86 x 5.86	<b>Sensing Area, H x V (mm):</b>	11.25 x 7.03
<b>Imaging Sensor:</b>	Sony IMX249	<b>Type of Sensor:</b>	Progressive Scan CMOS
<b>Shutter Type:</b>	Global	<b>Pixel Depth:</b>	10/12 bit
<b>Exposure Time:</b>	19µs - 3.9s	<b>Machine Vision Standard:</b>	USB3 Vision v1.0

### Electrical

Power Consumption (W):	Not Specified
------------------------	---------------

**Hardware & Interface Connectivity**

Interface:	USB 3.0		
Connector:	USB 3.1 Gen 1, Micro-B with Screw Locks	Power Supply:	Power over USB or via GPIO with <a href="#">#88-063</a>
GPIOs:	1 opto-isolated input, 1 opto-isolated output	Synchronization:	Hardware Trigger (GPIO) or Software Trigger
Interface Port Orientation:	Back Panel	GPIO Connector Type:	6-pin Hirose (HR10)

**Threading & Mounting**

Mount:	C-Mount	Mounting Threads:	1/4-20 with Tripod Mount Adapter <a href="#">#88-210</a>
--------	---------	-------------------	--

**Environmental & Durability Factors**

Operating Temperature (°C):	0 to +45	Storage Temperature (°C):	-30 to +60
-----------------------------	----------	---------------------------	------------

**Technical Information**

## Products

Type	Model Number	Sensor Format	Resolution (Megapixels)	Connector	Mount	Stock Number	Price	Buy
Color Camera	BFLY-U3-23S6C-C	1/1.2"	2.30	USB 3.1 Gen 1, Micro-B with Screw Locks	C-Mount	<a href="#">#33-433</a>	₹59,500	3 In Stock
Monochrome Camera	BFLY-U3-23S6M-C	1/1.2"	2.30	USB 3.1 Gen 1, Micro-B with Screw Locks	C-Mount	<a href="#">#33-432</a>	₹59,500	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038  
Phone: 1-800-363-1992 : [www.edmundoptics.com](http://www.edmundoptics.com)