




[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Iris Diaphragms](#)

## **TECHSPEC®** High Performance Motorizable Irises



- Fast Accurate Repeatable Motion
- Dual Control Gear and Lever Mechanics
- Removable Pin for OEM Integration
- Anti-Reflection (AR) Leaves Available
- Iris Diaphragm Mounts and Motor Sold Separately

Technical Information



## Products

| Minimum Aperture (mm) | Maximum Aperture (mm) | Outer Diameter (mm) | Number of Leaves | Construction                                       | Stock Number            | Price                     | Buy           |
|-----------------------|-----------------------|---------------------|------------------|----------------------------------------------------|-------------------------|---------------------------|---------------|
| 0.9                   | 7.0                   | 12.0                | 8                | Brass-Spring Steel                                 | <a href="#">#34-286</a> | ₹8,729<br>Qty 5+ ₹7,716   | 10 to 12 days |
| 0.9                   | 8.0                   | 14.8                | 8                | Brass-Spring Steel                                 | <a href="#">#34-287</a> | ₹5,355<br>Qty 5+ ₹4,724   | 10 to 12 days |
| 1.0                   | 12.0                  | 19.8                | 10               | Brass-Spring Steel                                 | <a href="#">#34-288</a> | ₹5,795<br>Qty 5+ ₹5,120   | 10 to 12 days |
| 1.2                   | 15.0                  | 24.0                | 12               | Brass-Spring Steel                                 | <a href="#">#34-289</a> | ₹5,795<br>Qty 5+ ₹5,120   | 10 to 12 days |
| 1.2                   | 18.0                  | 28.0                | 12               | Brass-Spring Steel                                 | <a href="#">#34-290</a> | ₹5,795<br>Qty 5+ ₹5,120   | 10 to 12 days |
| 1.4                   | 22.0                  | 33.0                | 14               | Brass-Spring Steel                                 | <a href="#">#34-291</a> | ₹7,262<br>Qty 5+ ₹6,440   | 10 to 12 days |
| 1.4                   | 25.0                  | 37.0                | 14               | Brass-Spring Steel                                 | <a href="#">#34-292</a> | ₹7,262<br>Qty 5+ ₹6,440   | 10 to 12 days |
| 1.5                   | 28.0                  | 40.0                | 16               | Brass-Spring Steel                                 | <a href="#">#34-293</a> | ₹7,628<br>Qty 5+ ₹6,734   | 10 to 12 days |
| 1.5                   | 34.0                  | 49.0                | 14               | Brass-Spring Steel                                 | <a href="#">#34-294</a> | ₹8,729<br>Qty 5+ ₹7,716   | 10 to 12 days |
| 0.9                   | 7.0                   | 12.0                | 8                | Brass-Spring Steel, Anti-Reflection (AR) Leaves    | <a href="#">#24-202</a> | ₹12,249<br>Qty 5+ ₹10,819 | 10 to 12 days |
| 1.0                   | 12.0                  | 19.8                | 10               | Brass-Spring Steel, Anti-Reflection (AR) Leaves    | <a href="#">#24-203</a> | ₹8,289<br>Qty 5+ ₹7,313   | 10 to 12 days |
| 1.4                   | 22.0                  | 33.0                | 14               | Brass-Spring Steel, Anti-Reflection (AR) Leaves    | <a href="#">#24-204</a> | ₹10,196<br>Qty 5+ ₹9,029  | 10 to 12 days |
| 1.5                   | 28.0                  | 40.0                | 16               | Aluminum-Spring Steel, Anti-Reflection (AR) Leaves | <a href="#">#24-205</a> | ₹10,856<br>Qty 5+ ₹9,572  | 10 to 12 days |
| 1.5                   | 34.0                  | 49.0                | 14               | Brass-Spring Steel, Anti-Reflection (AR) Leaves    | <a href="#">#24-206</a> | ₹12,249<br>Qty 5+ ₹10,819 | 10 to 12 days |





Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)