


[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® Cr Series Fixed Focal Length Lenses




- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Ruggedized (Cr) Designs (50g Shock) of our C Series Lens
- 3.5mm to 50mm Focal Length
- [Instrumentation \(Ci\) Versions](#) Also Available

Technical Information



1. Use a 2mm allen key to loosen the focus lock screw. Do not remove the lock screw from the mount.
2. By loosening the lock screw, you now have the ability to rotate the lens in and out of the C-Mount.
The focus will change as you rotate the lens – continue rotating the lens until you’ve reached the desired focus.
3. To secure the lens within the C-Mount at the desired focus, use the 2mm allen key to re-tighten the focus lock screw.

How to focus a Cr Series Lens



Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
3.50	1/1.8"	f/2	0 - ∞	C- Mount	#37-392	₹31,581	10 to 12 days
3.50	1/1.8"	f/2.8	0 - ∞	C- Mount	#37-393	₹31,581	Contact Us
3.50	1/1.8"	f/4	0 - ∞	C- Mount	#37-394	₹31,581	10 to 12 days
3.50	1/1.8"	f/5.6	0 - ∞	C- Mount	#37-395	₹31,581	10 to 12 days
3.50	1/1.8"	f/8	0 - ∞	C- Mount	#37-396	₹31,581	10 to 12 days
3.50	1/1.8"	f/11	0 - ∞	C- Mount	#37-397	₹31,581	10 to 12 days
4.50	1/1.8"	f/2	25 - ∞	C- Mount	#37-398	₹31,581	10 to 12 days
4.50	1/1.8"	f/2.8	25 - ∞	C- Mount	#37-399	₹31,581	Contact Us
4.50	1/1.8"	f/4	25 - ∞	C- Mount	#37-400	₹31,581	10 to 12 days
4.50	1/1.8"	f/5.6	25 - ∞	C- Mount	#37-401	₹31,581	10 to 12 days
4.50	1/1.8"	f/8	25 - ∞	C- Mount	#37-402	₹31,581	10 to 12 days
4.50	1/1.8"	f/11	25 - ∞	C- Mount	#37-403	₹31,581	10 to 12 days
6.00	1/1.8"	f/1.4	75 - ∞	C- Mount	#35-139	₹26,883	10 to 12 days
6.00	1/1.8"	f/1.8	75 - ∞	C- Mount	#35-140	₹26,883	10 to 12 days
6.00	1/1.8"	f/2.8	75 - ∞	C- Mount	#35-141	₹26,883	10 to 12 days
6.00	1/1.8"	f/4	75 - ∞	C- Mount	#35-142	₹26,883	10 to 12 days

6.00	1/1.8"	f/5.6	75 - ∞	C-Mount	#35-143	₹26,883	10 to 12 days
6.00	1/1.8"	f/8	75 - ∞	C-Mount	#35-144	₹26,883	10 to 12 days
8.50	2/3"	f/1.3	100 - ∞	C-Mount	#36-838	₹20,358	10 to 12 days
8.50	2/3"	f/1.8	100 - ∞	C-Mount	#36-839	₹20,358	10 to 12 days
8.50	2/3"	f/2.8	100 - ∞	C-Mount	#36-840	₹20,358	10 to 12 days
8.50	2/3"	f/4	100 - ∞	C-Mount	#36-841	₹20,358	10 to 12 days
8.50	2/3"	f/5.6	100 - ∞	C-Mount	#36-842	₹20,358	10 to 12 days
8.50	2/3"	f/8	100 - ∞	C-Mount	#36-843	₹20,358	10 to 12 days
12.00	2/3"	f/1.8	98 - ∞	C-Mount	#35-155	₹20,358	10 to 12 days
12.00	2/3"	f/2.8	98 - ∞	C-Mount	#35-156	₹20,358	10 to 12 days
12.00	2/3"	f/4	98 - ∞	C-Mount	#35-157	₹20,358	10 to 12 days
12.00	2/3"	f/5.6	98 - ∞	C-Mount	#35-158	₹20,358	10 to 12 days
12.00	2/3"	f/8	98 - ∞	C-Mount	#35-159	₹20,358	10 to 12 days
12.00	2/3"	f/11	98 - ∞	C-Mount	#35-160	₹20,358	10 to 12 days
12.00	2/3"	f/16	98 - ∞	C-Mount	#35-161	₹20,358	10 to 12 days
16.00	2/3"	f/1.6	98 - ∞	C-Mount	#35-163	₹20,358	10 to 12 days
16.00	2/3"	f/1.8	98 - ∞	C-Mount	#35-164	₹20,358	Contact Us
16.00	2/3"	f/2.8	98 - ∞	C-Mount	#35-165	₹20,358	10 to 12 days
16.00	2/3"	f/4	98 - ∞	C-Mount	#35-166	₹20,358	10 to 12 days

16.00	2/3"	f/5.6	98 - ∞	C-Mount	#35-167	₹20,358	7 days
16.00	2/3"	f/8	98 - ∞	C-Mount	#35-168	₹20,358	10 to 12 days
16.00	2/3"	f/11	98 - ∞	C-Mount	#35-169	₹20,358	10 to 12 days
16.00	2/3"	f/16	98 - ∞	C-Mount	#35-170	₹20,358	10 to 12 days
25.00	2/3"	f/1.4	98 - ∞	C-Mount	#35-172	₹20,358	10 to 12 days
25.00	2/3"	f/1.8	98 - ∞	C-Mount	#35-173	₹20,358	10 to 12 days
25.00	2/3"	f/2.8	98 - ∞	C-Mount	#35-174	₹20,358	10 to 12 days
25.00	2/3"	f/4	98 - ∞	C-Mount	#35-175	₹20,358	10 to 12 days
25.00	2/3"	f/5.6	98 - ∞	C-Mount	#35-176	₹20,358	10 to 12 days
25.00	2/3"	f/8	98 - ∞	C-Mount	#35-177	₹20,358	10 to 12 days
25.00	2/3"	f/11	98 - ∞	C-Mount	#35-178	₹20,358	10 to 12 days
25.00	2/3"	f/16	98 - ∞	C-Mount	#35-179	₹20,358	10 to 12 days
35.00	2/3"	f/1.65	165 - ∞	C-Mount	#35-181	₹20,358	10 to 12 days
35.00	2/3"	f/1.8	165 - ∞	C-Mount	#35-182	₹20,358	10 to 12 days
35.00	2/3"	f/2.8	165 - ∞	C-Mount	#35-183	₹20,358	10 to 12 days
35.00	2/3"	f/4.0	165 - ∞	C-Mount	#35-184	₹20,358	10 to 12 days
35.00	2/3"	f/5.6	165 - ∞	C-Mount	#35-185	₹20,358	10 to 12 days
35.00	2/3"	f/8.0	165 - ∞	C-Mount	#35-186	₹20,358	10 to 12 days

35.00	2/3"	f/11	165 - ∞	C- Mount	#35-187	₹20,358	10 to 12 days
35.00	2/3"	f/16	165 - ∞	C- Mount	#35-188	₹21,141	10 to 12 days
50.00	2/3"	f/2.0	250 - ∞	C- Mount	#35-190	₹26,883	10 to 12 days
50.00	2/3"	f/2.8	250 - ∞	C- Mount	#35-191	₹26,883	10 to 12 days
50.00	2/3"	f/4.0	250 - ∞	C- Mount	#35-192	₹26,883	10 to 12 days
50.00	2/3"	f/5.6	250 - ∞	C- Mount	#35-193	₹26,883	10 to 12 days
50.00	2/3"	f/8.0	250 - ∞	C- Mount	#35-194	₹26,883	10 to 12 days
50.00	2/3"	f/11	250 - ∞	C- Mount	#35-195	₹26,883	Contact Us
50.00	2/3"	f/16	250 - ∞	C- Mount	#35-196	₹26,883	10 to 12 days
100.00	1"	f/2.8	750 - ∞	C- Mount	#15-521	₹31,059	Contact Us
100.00	1"	f/4	750 - ∞	C- Mount	#15-522	₹31,059	Contact Us
100.00	1"	f/5.6	750 - ∞	C- Mount	#15-523	₹31,059	10 to 12 days
100.00	1"	f/8	750 - ∞	C- Mount	#15-524	₹31,059	10 to 12 days
100.00	1"	f/11	750 - ∞	C- Mount	#15-525	₹31,059	10 to 12 days
100.00	1"	f/16	750 - ∞	C- Mount	#15-526	₹31,059	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com