

[All Products](#) / [Optomechanics](#) / [Tube System](#) / [C, S, and T-Mount Components](#)

TECHSPEC® C, S, and T-Mount Circular Optic Mounts





- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

Common Specifications


General

Type of Optics:		Function:	
Circular		Optic Mount (Fixed)	


Technical Information




C-Mount Achromat/Thick Lens Mounts




C-Thread Simple / Thin Lens Mount




C-Thread Achromat / Thick Lens Mount




S-Thread Simple / Thin Lens Mount




C-Thread Achromat / Thick Lens Mount





S-Thread Simple /Thin Lens Mount



S-Thread Achromat / Thick Lens Mount





#58-741

Products

Thread Type	Diameter of Compatible Optics (mm)	Max. Thickness of Compatible Optics (mm)	Min. Thickness of Compatible Optics (mm)	Extension Length (mm)	Stock Number	Price	Buy
C-Mount	25.0 - 25.4	3.75	1.0	16.3	#56-353	₹7,188 Qty 5+ ₹6,381	10 to 12 days
C-Mount	21.0	3.0	1.0	5.6	#53-860	₹3,961 Qty 5+ ₹3,499	10 to 12 days
C-Mount	20.0	2.90	1.00	5.6	#54-618	₹3,961 Qty 5+ ₹3,521	7 days
C-Mount	18.0	3.0	1.0	5.6	#54-617	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	15.0	3.0	1.0	5.6	#54-616	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	12.5	3.0	1.0	5.6	#55-246	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	12.0	3.0	1.0	5.6	#54-615	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	10.0	3.0	1.0	5.6	#63-979	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	9.0	3.0	1.0	5.6	#54-614	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	6.5	3.0	1.0	5.6	#57-973	₹3,961 Qty 5+ ₹3,785	10 to 12 days
C-Mount	6.0	3.0	1.0	5.6	#54-613	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	5.0	3.0	1.0	5.6	#54-612	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	4.0	3.0	1.0	5.6	#57-972	₹3,961 Qty 5+ ₹3,719	10 to 12 days
C-Mount	3.0	3.0	1.0	5.6	#54-611	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	3.0	11.0	1.5	14.0	#54-620	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	5.0	6.5	1.0	14.0	#57-974	₹3,961 Qty 5+ ₹3,785	10 to 12 days

C-Mount	6.25	11.0	2.5	14.0	#54-621	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	9.0	11.0	2.5	14.0	#54-622	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	10.0	10.5	2.0	14.0	#63-980	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	12.5	11.0	2.5	14.0	#54-623	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	15.0	11.0	3.0	14.0	#54-624	₹3,961 Qty 5+ ₹3,521	7 days
C-Mount	18.0	11.0	3.0	14.0	#54-625	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	20.0	11.0	3.5	14.0	#54-626	₹3,961 Qty 5+ ₹3,521	10 to 12 days
C-Mount	25.0 - 25.4	11.5	3.3	24.2	#56-354	₹7,188 Qty 5+ ₹6,381	Contact Us
S-Mount	3.0	3.0	1.0	6.2	#63-938	₹2,714 Qty 5+ ₹2,435	10 to 12 days
S-Mount	4.0	3.0	1.0	6.2	#63-939	₹2,714 Qty 5+ ₹2,435	10 to 12 days
S-Mount	5.0	3.0	1.0	5.6	#63-940	₹2,714 Qty 5+ ₹2,435	10 to 12 days
S-Mount	6.0	3.0	1.0	5.6	#63-941	₹2,714 Qty 5+ ₹2,435	10 to 12 days
S-Mount	9.0	3.0	1.0	5.6	#63-942	₹2,714 Qty 5+ ₹2,435	10 to 12 days
S-Mount	10.0	2.5	1.0	8.6	#63-943	₹2,714 Qty 5+ ₹2,435	10 to 12 days
S-Mount	12.5 - 12.7	2.5	1.0	13.6	#63-944	₹4,474 Qty 5+ ₹3,976	10 to 12 days
S-Mount	5.0	6.5	1.0	9.7	#63-948	₹2,714 Qty 5+ ₹2,435	10 to 12 days
S-Mount	6.25	6.5	2.0	9.7	#63-949	₹2,714 Qty 5+ ₹2,435	10 to 12 days
S-Mount	9.0	6.5	2.0	9.7	#63-950	₹2,714 Qty 5+ ₹2,435	10 to 12 days
S-Mount	10.0	6.5	2.0	12.7	#63-951	₹2,714 Qty 5+ ₹2,435	10 to 12 days
S-Mount	12.5 - 12.7	6.5	2.0	20.5	#63-952	₹4,474 Qty 5+ ₹3,976	10 to 12 days

T-Mount	12.5 - 12.7	5.50	2.00	11.5	#52-933	₹4,804 Qty 5+ ₹4,518	10 to 12 days
T-Mount	25.0 - 25.4	5.50	2.00	11.5	#52-292	₹4,804 Qty 5+ ₹4,276	10 to 12 days
T-Mount	27.0	5.5	2.0	11.5	#53-861	₹4,804 Qty 5+ ₹4,276	10 to 12 days
T-Mount	30.0	5.5	2.5	11.5	#57-975	₹4,804 Qty 5+ ₹4,276	10 to 12 days
T-Mount	40.0	10.95	2.0	15.0	#57-976	₹4,804 Qty 5+ ₹4,276	10 to 12 days
T-Mount	12.5 - 12.7	15.50	5.00	21.5	#52-954	₹4,804 Qty 5+ ₹4,276	10 to 12 days
T-Mount	25.0 - 25.4	15.50	5.00	21.5	#52-293	₹4,804 Qty 5+ ₹4,276	10 to 12 days
T-Mount	30.0	15.5	5.0	21.5	#57-977	₹4,804 Qty 5+ ₹4,276	Contact Us
T-Mount	40.0	20.95	5.0	25.0	#57-978	₹4,804 Qty 5+ ₹4,276	10 to 12 days
T-Mount	50.0	10.0	2.0	22.0	#88-943	₹7,188 Qty 5+ ₹6,249	10 to 12 days
T-Mount	50.0	18.5	5.0	32.5	#88-944	₹7,188 Qty 5+ ₹6,249	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com