


[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Optical Diffusers](#)

Light Diffusing Film



- Diffusion of UV to NIR Illumination
- Flexible Polymer Substrate
- Easily Cut to Size
- [Glass Diffusers](#) Also Available

Common Specifications

General

Note:

Protective film on non-matte surface should be removed before use

Physical & Mechanical Properties

Thickness (mm): 0.13 ±0.005

Optical Properties

Coating: Uncoated


Wavelength Range (nm): 300 - 1100

Environmental & Durability Factors


Operating Temperature (°C): Up to Approx. +100°C

Technical Information

Light Diffusing Film



Relative Intensity vs. Angle Light Diffusing Film



Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Stock Number	Price	Buy
12.50	-	0.13	#27-086	₹1,137 Qty 11+ ₹1,027	10 to 12 days
25.00	-	0.13	#27-089	₹1,339 Qty 11+ ₹1,210	10 to 12 days
50.00	-	0.13	#27-092	₹1,412 Qty 11+ ₹1,284	10 to 12 days
75.00	-	0.13	#27-095	₹1,522 Qty 11+ ₹1,375	10 to 12 days
-	12.5 x 12.5	0.13	#27-102	₹1,137 Qty 11+ ₹1,027	10 to 12 days
-	25 x 25	0.13	#27-103	₹1,339 Qty 11+ ₹1,210	10 to 12 days
-	50 x 50	0.13	#27-108	₹1,412 Qty 11+ ₹1,284	10 to 12 days
-	75 x 75	0.13	#27-110	₹1,522 Qty 11+ ₹1,375	10 to 12 days
-	100 x 100	0.13	#17-683	₹1,632 Qty 11+ ₹1,467	10 to 12 days
-	150 x 150	0.13	#20-219	₹2,677 Qty 11+ ₹2,402	10 to 12 days
-	200 x 200	0.13	#20-220	₹3,429 Qty 11+ ₹3,081	10 to 12 days
-	250 x 250	0.13	#20-247	₹4,951 Qty 11+ ₹4,474	10 to 12 days
-	300 x 300	0.13	#17-682	₹5,721 Qty 11+ ₹5,135	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com