


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Convex \(PCX\) Lenses](#) / [Fused Silica Plano-Convex \(PCX\) Lenses](#)

TECHSPEC®

UV Fused Silica Plano-Convex (PCX) Lenses - NIR I Coated



- AR Coated to Provide <0.5% Reflection per Surface for 600 - 1050nm
- Precision Fused Silica Substrate
- Various Coating Options: [Uncoated](#), [MgF₂](#), [UV-AR](#), [UV-VIS](#), [VIS-EXT](#), [VIS-NIR](#), [VIS 0°](#), [YAG-BBAR](#), and [NIR II](#)

Common Specifications

Physical & Mechanical Properties

Bevel: Protective bevel as needed

Optical Properties

Coating: NIR I (600-1050nm)

Substrate: [Fused Silica](#) (Corning 7980)

Surface Quality: 40-20

Power (P-V) @ 632.8nm: 3 Rings

Irregularity (P-V) @ 632.8nm: 0.5 Rings

Focal Length Tolerance (%): ±1

Wavelength Range (nm): 600 - 1050

Technical Information

Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
5.00	10.00	8.63	NIR I (600-1050nm)	Fused Silica	#18-255	₹10,588 Qty 6+ ₹8,486	10 to 12 days
5.00	15.00	13.83	NIR I (600-1050nm)	Fused Silica	#18-260	₹9,965 Qty 6+ ₹7,941	10 to 12 days
5.00	25.00	23.97	NIR I (600-1050nm)	Fused Silica	#18-270	₹9,965 Qty 6+ ₹7,941	10 to 12 days
6.00	9.00	7.29	NIR I (600-1050nm)	Fused Silica	#18-010	₹10,743 Qty 6+ ₹8,564	10 to 12 days
6.00	12.00	10.63	NIR I (600-1050nm)	Fused Silica	#18-015	₹10,743 Qty 6+ ₹8,564	10 to 12 days
6.00	15.00	13.63	NIR I (600-1050nm)	Fused Silica	#18-115	₹10,354 Qty 6+ ₹8,252	10 to 12 days
6.00	18.00	16.62	NIR I (600-1050nm)	Fused Silica	#18-020	₹10,354 Qty 6+ ₹8,252	10 to 12 days
6.00	24.00	22.63	NIR I (600-1050nm)	Fused Silica	#26-330	₹10,354 Qty 6+ ₹8,252	10 to 12 days
9.00	12.00	9.26	NIR I (600-1050nm)	Fused Silica	#18-125	₹10,977 Qty 6+ ₹8,797	10 to 12 days
9.00	13.50	11.44	NIR I (600-1050nm)	Fused Silica	#18-025	₹10,977 Qty 6+ ₹8,797	10 to 12 days
9.00	18.00	15.94	NIR I (600-1050nm)	Fused Silica	#18-030	₹10,977 Qty 6+ ₹8,797	10 to 12 days
9.00	22.00	19.94	NIR I (600-1050nm)	Fused Silica	#17-960	₹10,588 Qty 6+ ₹8,486	10 to 12 days
9.00	27.00	25.63	NIR I (600-1050nm)	Fused Silica	#18-035	₹10,588 Qty 6+ ₹8,486	10 to 12 days
9.00	36.00	34.63	NIR I (600-1050nm)	Fused Silica	#26-331	₹10,588 Qty 6+ ₹8,486	10 to 12 days
10.00	20.00	17.94	NIR I (600-1050nm)	Fused Silica	#17-965	₹11,133 Qty 6+ ₹8,875	10 to 12 days
10.00	25.00	22.94	NIR I (600-1050nm)	Fused Silica	#26-332	₹11,133 Qty 6+ ₹8,875	10 to 12 days

12.00	18.00	15.26	NIR I (600-1050nm)	Fused Silica	#18-135	₹11,366 Qty 6+ ₹9,108	10 to 12 days
12.00	25.00	22.31	NIR I (600-1050nm)	Fused Silica	#18-040	₹11,366 Qty 6+ ₹9,108	Contact Us
12.00	30.00	27.56	NIR I (600-1050nm)	Fused Silica	#18-045	₹10,977 Qty 6+ ₹8,797	10 to 12 days
12.00	36.00	34.29	NIR I (600-1050nm)	Fused Silica	#18-140	₹10,977 Qty 6+ ₹8,797	Contact Us
12.00	40.00	37.85	NIR I (600-1050nm)	Fused Silica	#18-050	₹10,977 Qty 6+ ₹8,797	10 to 12 days
12.00	50.00	48.01	NIR I (600-1050nm)	Fused Silica	#18-055	₹10,354 Qty 6+ ₹8,252	10 to 12 days
12.00	72.00	70.29	NIR I (600-1050nm)	Fused Silica	#17-975	₹10,354 Qty 6+ ₹8,252	10 to 12 days
12.00	100.00	98.33	NIR I (600-1050nm)	Fused Silica	#18-060	₹10,354 Qty 6+ ₹8,252	10 to 12 days
15.00	25.00	22.09	NIR I (600-1050nm)	Fused Silica	#26-335	₹11,911 Qty 6+ ₹9,498	10 to 12 days
15.00	30.00	27.53	NIR I (600-1050nm)	Fused Silica	#18-210	₹11,911 Qty 6+ ₹9,498	10 to 12 days
15.00	45.00	42.94	NIR I (600-1050nm)	Fused Silica	#18-215	₹11,522 Qty 6+ ₹9,186	10 to 12 days
15.00	60.00	57.94	NIR I (600-1050nm)	Fused Silica	#18-220	₹11,522 Qty 6+ ₹9,186	Contact Us
15.00	75.00	72.94	NIR I (600-1050nm)	Fused Silica	#26-336	₹11,522 Qty 6+ ₹9,186	10 to 12 days
18.00	27.00	23.23	NIR I (600-1050nm)	Fused Silica	#17-985	₹11,911 Qty 6+ ₹9,498	10 to 12 days
18.00	36.00	32.92	NIR I (600-1050nm)	Fused Silica	#26-071	₹11,911 Qty 6+ ₹9,498	10 to 12 days
20.00	30.00	25.88	NIR I (600-1050nm)	Fused Silica	#18-150	₹12,300 Qty 6+ ₹9,809	10 to 12 days
20.00	40.00	36.92	NIR I (600-1050nm)	Fused Silica	#18-160	₹12,300 Qty 6+ ₹9,809	10 to 12 days
20.00	50.00	47.25	NIR I (600-1050nm)	Fused Silica	#18-165	₹11,911 Qty 6+ ₹9,498	10 to 12 days
20.00	60.00	57.60	NIR I (600-1050nm)	Fused Silica	#18-170	₹11,911 Qty 6+ ₹9,498	10 to 12 days

20.00	80.00	77.95	NIR I (600-1050nm)	Fused Silica	#18-175	₹11,911 Qty 6+ ₹9,498	10 to 12 days
25.00	35.00	29.17	NIR I (600-1050nm)	Fused Silica	#26-072	₹12,534 Qty 6+ ₹10,043	10 to 12 days
25.00	38.00	33.03	NIR I (600-1050nm)	Fused Silica	#18-065	₹12,534 Qty 6+ ₹10,043	10 to 12 days
25.00	40.00	34.86	NIR I (600-1050nm)	Fused Silica	#18-005	₹12,534 Qty 6+ ₹10,043	10 to 12 days
25.00	50.00	46.00	NIR I (600-1050nm)	Fused Silica	#18-070	₹12,534 Qty 6+ ₹10,043	10 to 12 days
25.00	60.00	56.92	NIR I (600-1050nm)	Fused Silica	#18-145	₹12,145 Qty 6+ ₹9,731	10 to 12 days
25.00	75.00	71.96	NIR I (600-1050nm)	Fused Silica	#18-075	₹12,145 Qty 6+ ₹9,731	10 to 12 days
25.00	100.00	97.40	NIR I (600-1050nm)	Fused Silica	#18-080	₹12,145 Qty 6+ ₹9,731	10 to 12 days
25.00	125.00	122.65	NIR I (600-1050nm)	Fused Silica	#18-085	₹11,522 Qty 6+ ₹9,186	10 to 12 days
25.00	150.00	147.82	NIR I (600-1050nm)	Fused Silica	#18-090	₹11,522 Qty 6+ ₹9,186	10 to 12 days
25.00	175.00	172.94	NIR I (600-1050nm)	Fused Silica	#18-095	₹11,522 Qty 6+ ₹9,186	10 to 12 days
25.00	200.00	198.02	NIR I (600-1050nm)	Fused Silica	#18-100	₹11,522 Qty 6+ ₹9,186	10 to 12 days
25.00	250.00	248.14	NIR I (600-1050nm)	Fused Silica	#18-105	₹11,522 Qty 6+ ₹9,186	10 to 12 days
25.00	400.00	398.33	NIR I (600-1050nm)	Fused Silica	#18-110	₹11,522 Qty 6+ ₹9,186	Contact Us
30.00	50.00	45.2	NIR I (600-1050nm)	Fused Silica	#18-230	₹15,103 Qty 6+ ₹12,067	10 to 12 days
30.00	90.00	86.57	NIR I (600-1050nm)	Fused Silica	#18-240	₹14,714 Qty 6+ ₹11,755	10 to 12 days
30.00	120.00	116.57	NIR I (600-1050nm)	Fused Silica	#18-245	₹14,714 Qty 6+ ₹11,755	10 to 12 days
30.00	150.00	146.57	NIR I (600-1050nm)	Fused Silica	#18-250	₹14,324 Qty 6+ ₹11,444	10 to 12 days
50.00	75.00	66.43	NIR I (600-1050nm)	Fused Silica	#18-180	₹23,666 Qty 6+ ₹18,918	10 to 12 days

50.00	100.00	93.84	NIR I (600-1050nm)	Fused Silica	#18-185	₹23,666 Qty 6+ ₹18,918	10 to 12 days
50.00	150.00	145.20	NIR I (600-1050nm)	Fused Silica	#18-190	₹23,277 Qty 6+ ₹18,606	10 to 12 days
50.00	200.00	195.19	NIR I (600-1050nm)	Fused Silica	#18-195	₹23,277 Qty 6+ ₹18,606	Contact Us
50.00	250.00	245.21	NIR I (600-1050nm)	Fused Silica	#18-200	₹23,277 Qty 6+ ₹18,606	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com