


[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Visible Windows](#)

Acrylic (PMMA) Plastic Windows



- Highly Scratch-Resistant
- High Visible Light Transmission
- Cost-Effective Alternative to Glass
- [Polycarbonate Plastic Windows](#) Also Available

Common Specifications

Physical & Mechanical Properties

Bevel: Protective as needed

Edges: Smooth, Machined

Optical Properties

Abbe Number (v_d): 58

Coating: Uncoated

Index of Refraction (n_d): 1.49



Substrate: PMMA

Wavelength Range (nm): 400 - 1600

Material Properties

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$): 60

Technical Information



Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
25.40	-	1.52	Uncoated	#19-634	₹1,687 Qty 6+ ₹1,339	10 to 12 days
38.10	-	1.52	Uncoated	#71-541	₹1,907 Qty 6+ ₹1,522	10 to 12 days
50.80	-	1.52	Uncoated	#19-635	₹2,054 Qty 6+ ₹1,632	10 to 12 days
63.50	-	1.52	Uncoated	#71-542	₹2,292 Qty 6+ ₹1,834	10 to 12 days
-	50.80 x 50.80	1.52	Uncoated	#19-636	₹2,054 Qty 6+ ₹1,632	10 to 12 days
76.20	-	1.52	Uncoated	#19-637	₹2,476 Qty 6+ ₹1,980	10 to 12 days
-	76.20 x 76.20	1.52	Uncoated	#19-638	₹2,476 Qty 6+ ₹1,980	10 to 12 days
-	101.6 x 127.0	1.52	Uncoated	#19-639	₹3,282 Qty 6+ ₹2,641	10 to 12 days
-	127.00 x 177.80	1.52	Uncoated	#71-543	₹3,998 Qty 6+ ₹3,191	10 to 12 days
-	203.2 x 254.0	1.52	Uncoated	#19-640	₹6,491 Qty 6+ ₹5,171	10 to 12 days
-	254.00 x 304.80	1.52	Uncoated	#71-544	₹9,169 Qty 6+ ₹7,335	10 to 12 days
-	304.80 x 355.60	1.52	Uncoated	#71-545	₹10,269 Qty 6+ ₹8,215	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com