

[All Products](#) / [Optics](#) / [SCHOTT Optical Components](#)

SCHOTT Calibrated Neutral Density (ND) Filters

See More by [SCHOTT Optical Components](#)



- Calibrated for Specific Wavelengths
- Optical Densities Ranging from 0.3 to 3.0
- NG3, NG4, NG5, NG9, or NG11 Glass Types

Common Specifications

Physical & Mechanical Properties

Dimensions (mm):	50.0 x 50.0 ±0.2	Clear Aperture CA (mm):	48.5 x 48.5
Parallelism (arcmin):	≤3	Edges:	Fine Grind
Bevel:	0.5 x 45°	Shape of Back Surface:	Plano

Optical Properties

Coating:	Uncoated	Surface Quality:	60-40
-----------------	----------	-------------------------	-------

Technical Information

Products

Glass/Filter Number	Optical Density OD (Average)	DWL (nm)	Stock Number	Price	Buy
SCHOTT NG11	0.3	405	#21-366	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG5	0.5	405	#21-367	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG4	1.0	405	#21-368	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG3	2.0	405	#21-369	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG3	3.0	405	#21-370	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG11	0.3	633	#21-371	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG5	0.5	633	#21-372	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG4	1.0	633	#21-373	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG3	2.0	633	#21-374	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG9	3.0	633	#21-375	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG11	0.3	785	#21-376	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG5	0.5	785	#21-377	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG4	1.0	785	#21-378	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG9	2.0	785	#21-379	₹13,390 Qty 10+ ₹11,989	10 to 12 days
SCHOTT NG9	3.0	785	#21-380	₹13,390 Qty 10+ ₹11,989	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com