

[All Products](#) / [Optics](#) / [Fiber Optics](#)

Single Mode Fiber Optic Patchcords



- FC/PC, FC/APC, and Hybrid Terminated Connectors
- Patchcords for Wavelengths from 450 – 1650nm
- 1m, 2m and 5m Standardized Lengths Available

Common Specifications

Physical & Mechanical Properties

Jacket Material:

900µm Yellow Hytrel® Tubing

Optical Properties

Numerical Aperture NA:

0.13

Technical Information

Products

Wavelength Range (nm)	Mode Field Diameter (nm)	NA	Connector	Length (m)	Stock Number	Price	Buy
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	1	#25-928	₹3,425 Qty 5+ ₹3,114	10 to 12 days
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	2	#25-929	₹3,581 Qty 5+ ₹3,192	10 to 12 days
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	5	#71-136	₹3,815	Contact Us
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	1	#25-930	₹5,294 Qty 5+ ₹4,749	10 to 12 days
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	2	#25-931	₹5,761 Qty 5+ ₹5,216	10 to 12 days
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	5	#71-137	₹6,462	10 to 12 days
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	1	#25-932	₹7,007 Qty 5+ ₹6,306	10 to 12 days
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	2	#25-933	₹7,551 Qty 5+ ₹6,773	10 to 12 days
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	5	#71-138	₹8,408	10 to 12 days
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC	1	#25-934	₹5,527 Qty 5+ ₹4,982	10 to 12 days
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC	2	#25-935	₹5,683 Qty 5+ ₹5,138	10 to 12 days
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/PC	5	#71-139	₹5,917	10 to 12 days

450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC	1	#25-936	₹6,228 Qty 5+ ₹5,605	10 to 12 days
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC	2	#25-937	₹6,695 Qty 5+ ₹5,994	10 to 12 days
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/PC	5	#71-140	₹7,396	10 to 12 days
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	1	#25-938	₹5,372 Qty 5+ ₹4,827	10 to 12 days
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	2	#25-939	₹5,527 Qty 5+ ₹4,982	10 to 12 days
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	5	#71-141	₹5,761	10 to 12 days
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	1	#25-940	₹8,719 Qty 5+ ₹7,863	10 to 12 days
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	2	#25-941	₹9,108 Qty 5+ ₹8,174	10 to 12 days
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	5	#71-142	₹9,731	10 to 12 days
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	1	#25-942	₹9,031 Qty 5+ ₹8,096	7 days
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	2	#25-943	₹9,498 Qty 5+ ₹8,564	10 to 12 days
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	5	#71-143	₹10,198	10 to 12 days
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/APC	1	#25-944	₹7,318 Qty 5+ ₹6,617	10 to 12 days
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/APC	2	#25-945	₹7,474 Qty 5+ ₹6,695	10 to 12 days
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/APC	5	#71-144	₹7,707	10 to 12 days

450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/APC	1	#25-946	₹8,096 Qty 5+ ₹7,318	10 to 12 days
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/APC	2	#25-947	₹8,408 Qty 5+ ₹7,551	10 to 12 days
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/APC	5	#71-145	₹8,875	10 to 12 days
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC to FC/APC	1	#25-948	₹4,437 Qty 5+ ₹3,970	10 to 12 days
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC to FC/APC	5	#71-146	₹4,827	10 to 12 days
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC to FC/APC	1	#25-949	₹7,785 Qty 5+ ₹7,007	10 to 12 days
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC to FC/APC	5	#71-147	₹8,953	10 to 12 days
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC to FC/APC	1	#25-950	₹8,252 Qty 5+ ₹7,396	10 to 12 days
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC to FC/APC	5	#71-148	₹9,653	10 to 12 days
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC to FC/APC	1	#25-951	₹6,773 Qty 5+ ₹6,072	10 to 12 days
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/PC to FC/APC	5	#71-149	₹7,162	10 to 12 days
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC to FC/APC	1	#25-952	₹7,629 Qty 5+ ₹6,851	10 to 12 days
			FC/PC to FC/APC	5	#71-150	₹8,797	10 to 12 days



Edmund
optics | worldwide

Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com