

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Convex \(PCX\) Lenses](#) / [UV and IR Plano-Convex \(PCX\) Lenses](#)

ISP Optics Germanium (Ge) Plano-Convex (PCX) Lenses See

More by [ISP Optics](#)



- Ideal for Thermal Imaging Applications
- Uncoated Transmission from 2 – 16μm
- Available Uncoated or BBAR Coated for 3 - 12μm
- Due to material supply chain disruptions with germanium, there may be increased lead times and price changes on our germanium products. For more information, please contact our [customer service team](#).
- Edmund Optics has limited remaining inventory of this part number and no raw material available to supply more once this is depleted. Please contact our Product Support Engineers to help with an alternate solution for your needs. Customer Service can provide you the latest price and availability.

Common Specifications

Physical & Mechanical Properties

Centering (arcmin): <3

Bevel: Protective as needed

Optical Properties

Substrate: [Germanium \(Ge\)](#)

Surface Quality: 60-40

Irregularity (P-V) @ 10.6μm: λ/20

Focal Length Tolerance (%): ±2

Technical Information

Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Model Number	Stock Number	Price	Buy
12.70	50.80	-	Uncoated	GE-PX-12-50	#24-844	₹19,575	10 to 12 days
25.40	63.50	-	Uncoated	GE-PX-25-63	#24-846	₹35,235	Contact Us
25.40	75.00	-	Uncoated	GE-PX-25-76	#24-847	₹35,235	Contact Us
25.40	127.00	-	Uncoated	GE-PX-25-127	#24-848	₹31,842	10 to 12 days
25.40	150.00	-	Uncoated	GE-PX-25-150	#24-849	₹31,842	10 to 12 days
25.40	200.00	-	Uncoated	GE-PX-25-200	#24-850	₹31,842	10 to 12 days
25.40	254.00	-	Uncoated	GE-PX-25-254	#24-851	₹31,842	10 to 12 days
38.10	50.80	-	Uncoated	GE-PX-38-50	#24-852	₹64,380	10 to 12 days
38.10	63.50	-	Uncoated	GE-PX-38-63	#24-853	₹64,380	10 to 12 days
38.10	75.00	-	Uncoated	GE-PX-38-76	#24-854	₹64,380	10 to 12 days
38.10	100.00	-	Uncoated	GE-PX-38-100	#24-855	₹64,380	10 to 12 days
38.10	127.00	-	Uncoated	GE-PX-38-127	#24-856	₹64,380	10 to 12 days
38.10	254.00	-	Uncoated	GE-PX-38-254	#24-858	₹64,380	10 to 12 days
38.10	1,000.00	-	Uncoated	GE-PX-38-1000	#24-859	₹64,380	10 to 12 days
50.80	75.00	-	Uncoated	GE-PX-50-76	#24-860	₹80,910	10 to 12 days
50.80	100.00	-	Uncoated	GE-PX-50-100	#24-861	₹80,910	10 to 12 days

50.80	127.00	-	Uncoated	GE-PX-50-127	#24-862	₹80,910	10 to 12 days
50.80	200.00	-	Uncoated	GE-PX-50-200	#24-863	₹80,910	10 to 12 days
50.80	300.00	-	Uncoated	GE-PX-50-300	#24-864	₹80,910	10 to 12 days
25.40	75.00	-	BBAR (3000-12000nm)	AR312-GE-PX-25-76	#24-872	₹65,685	10 to 12 days
25.40	127.00	-	BBAR (3000-12000nm)	AR312-GE-PX-25-127	#24-874	₹65,685	10 to 12 days
25.40	150.00	-	BBAR (3000-12000nm)	AR312-GE-PX-25-150	#24-875	₹65,685	10 to 12 days
25.40	254.00	-	BBAR (3000-12000nm)	AR312-GE-PX-25-254	#24-877	₹65,250	10 to 12 days
25.40	500.00	-	BBAR (3000-12000nm)	AR312-GE-PX-25-500	#24-878	₹65,685	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com