


[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Dielectric Coatings](#)

TECHSPEC®

# Broadband Dielectric Elliptical Flat Mirrors



- Circular Profile When Oriented at 45°
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Enhanced Reflectivity and LIDT over Metallic Coatings

## Common Specifications

### General

Note:

Flatness specification is Peak to Valley

### Optical Properties

Coating Type:

Dielectric

Surface Flatness (P-V):

λ/8

Substrate:



BOROFLOAT®

Surface Quality:

60-40

**Technical Information**

Products

Wavelength Range (nm)	Minor Axis (mm)	Major Axis (mm)	Dimensional Tolerance (mm)	Thickness (mm)	Stock Number	Price	Buy
<a href="#">#72-933 New</a>							
							
New							
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!							
320 - 450	12.70	17.96	±0.38	3.81		₹9,342 Qty 6+ ₹7,474	10 to 12 days
<a href="#">#72-934 New</a>							
							
New							
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!							
320 - 450	22.23	31.42	±0.38	6.35		₹10,899 Qty 6+ ₹8,719	10 to 12 days

[#72-935 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

320 - 450

26.97

38.15

±0.38

6.35

₹10,899  
Qty 6+ ₹8,719

10 to 12 days

---

[#72-941 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

320 - 450

76.20

107.77

±0.50

19.05

₹48,656  
Qty 6+ ₹38,925

10 to 12 days

---

[#72-942 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

400 - 750

12.70

17.96

±0.38

3.81

₹7,785  
Qty 6+ ₹6,228

10 to 12 days

---

[#72-943 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

400 - 750

22.23

31.42

±0.38

6.35

₹9,342  
Qty 6+ ₹7,474

10 to 12 days

---

[#72-944 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

400 - 750

26.97

38.15

±0.38

6.35

₹9,342  
Qty 6+ ₹7,474

10 to 12 days

---

[#72-950 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

400 - 750

76.20

107.77

±0.50

19.05

₹44,375  
Qty 6+ ₹35,422

Contact Us

---

[#72-951 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

750 - 1100

12.70

17.96

±0.38

3.81

₹7,785  
Qty 6+ ₹6,228

10 to 12 days

---

[#72-952 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

750 - 1100

22.23

31.42

±0.38

6.35

₹9,342  
Qty 6+ ₹7,474

10 to 12 days

---

[#72-953 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

750 - 1100 26.97 38.15 ±0.38 6.35

₹9,342  
Qty 6+ ₹7,474

10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)

[#72-959 New](#)



New

Launched  
on our  
website  
before  
appearing  
in our  
latest print  
catalogs.  
Be the  
first to buy  
before  
anyone  
else!

750 - 1100 76.20 107.77 ±0.50 19.05

₹44,375  
Qty 6+ ₹35,422

Contact Us