

TECHSPEC<sup>®</sup> 10mm Diameter, C-Mount Thin Optic Mount



Stock #63-979 1 In Stock

-

1

+

₹3,961

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | ₹3,961 each                   |
| Qty 5-9        | ₹3,521 each                   |
| Qty 10-25      | ₹3,264 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General             |                 |
|---------------------|-----------------|
| Fixed               | Type:           |
| Circular            | Type of Optics: |
| Optic Mount (Fixed) | Function:       |

| Physical & Mechanical Properties    |                                           |
|-------------------------------------|-------------------------------------------|
| 5.6                                 | Extension Length (mm):                    |
| Black Anodized Aluminum (6061 T6)   | Construction:                             |
| 9.6                                 | Total Length (mm):                        |
| 30.0                                | Outer Diameter (mm):                      |
| 9.0                                 | Clear Aperture CA (mm):                   |
| 3.0                                 | Max. Thickness of Compatible Optics (mm): |
| 1.0                                 | Min. Thickness of Compatible Optics (mm): |
| Threading & Mounting                |                                           |
| 10.0                                | Diameter of Compatible Optics (mm):       |
| C-Mount                             | Thread Type:                              |
| Regulatory Compliance               |                                           |
| Compliant                           | RoHS 2015:                                |
| View                                | Certificate of Conformance:               |
| Compliant                           | REACH 241:                                |
| China                               | Country of Origin:                        |
| Edmund Optics India Private Limited | Imported By:                              |

## Product Details

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

**Note:** [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

## Technical Information

