

[See all 15 Products in Family](#)

15mm Diameter, Outdoor, Hydrophobic Window

See More by [SCHOTT Optical Components](#)



Stock #34-525 [CONTACT US](#)

- 1 + MRP ₹9,080

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹9,080 each
Qty 6-25	₹8,173 each
Qty 26-99	₹7,769 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**

Glass **Type of Window:**

Outdoor **Note:**

Physical & Mechanical Properties

13.50 **Clear Aperture CA (mm):**

15.00 +0.00/-0.25 **Diameter (mm):**

1.10 ±0.1 **Thickness (mm):**

Protective as needed **Bevel:**

90.00 **Clear Aperture (%):**

Fine Ground **Edges:**

0.20 **Poisson's Ratio:**

64 **Young's Modulus (GPa):**

480.00 **Knoop Hardness (kg/mm²):**

Optical Properties

Hydrophobic (425-675nm) **Coating:**

BOROFLOAT® **Substrate:**

1.472 **Index of Refraction (n_d):**

80-50 **Surface Quality:**

65.41 **Abbe Number (v_d):**

R_{avg} <0.5% @ 425 - 675nm **Coating Specification:**

425 - 675 **Wavelength Range (nm):**

Material Properties

2.23 **Density (g/cm³):**

3.25 **Coefficient of Thermal Expansion CTE (10⁻⁶/°C):**

Water: 90 - 110
Oil: 75 - 80 **Contact Angle (°):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

United States **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).



Product Details

- Oil and Water Repellent Coating
- Ideal for Industrial and Harsh Environments
- AR Coated for <0.5% Reflection in the Visible Spectrum

Hydrophobic Windows are designed to repel oil (oleophobic) and other liquids (hydrophobic), facilitating cleaning and ensuring maximum transmission of incident light. Hydrophobic treated surfaces cause liquids to form droplets on contact rather than be absorbed or spread across the surface of the optic. Hydrophobic Windows feature anti-reflection coatings to provide less than 0.5% reflection per surface from 425 – 675nm. These windows are ideal for harsh environments, portable handheld devices, or biometric measurement devices.

Indoor Hydrophobic Windows are ideal for applications where cleaning or abrasion is expected while Outdoor Hydrophobic Windows provide better performance both at elevated temperatures and under direct UV light exposure.

Technical Information



Compatible Mounts