

TECHSPEC<sup>®</sup> 15X Arcturus® HeNe Beam Expander



15X HeNe Fixed Beam Expander, #58-209

Stock **#58-209** [CONTACT US](#)

-

1

+

₹51,750

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | ₹51,750 each                  |
| Qty 5-24       | ₹45,900 each                  |
| Qty 25-99      | ₹40,950 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

SPECIFICATIONS

General

Beam Expander

Type:

Style:

|                                                                              |                                     |
|------------------------------------------------------------------------------|-------------------------------------|
| Fixed Magnification                                                          |                                     |
| Physical & Mechanical Properties                                             |                                     |
| 120.50                                                                       | Length (mm):                        |
| 461                                                                          | Weight (g):                         |
| 50                                                                           | Housing Diameter (mm):              |
| Optical Properties                                                           |                                     |
| 0                                                                            | Angle of Incidence (°):             |
| BBAR (450-750nm)                                                             | Coating:                            |
| 633                                                                          | Design Wavelength DWL (nm):         |
| 2                                                                            | Entrance Aperture (mm):             |
| 27                                                                           | Exit Aperture (mm):                 |
| 15X                                                                          | Expansion Power:                    |
| 1.2m - ∞                                                                     | Focus Range (mm):                   |
| Optical Glass                                                                | Substrate: <input type="checkbox"/> |
| <λ/4 @ 633nm for Input Beam ≤1mm                                             | Transmitted Wavefront, P-V:         |
| R <sub>abs</sub> <0.4% @ 630 - 670nm<br>R <sub>avg</sub> <0.6% @ 450 - 750nm | Coating Specification:              |
| 450 - 750                                                                    | Wavelength Range (nm):              |
| Non-Rotating Optics                                                          | Divergence Adjustment:              |
| Threading & Mounting                                                         |                                     |
| C-Mount                                                                      | Mounting Threads:                   |
| Regulatory Compliance                                                        |                                     |
| Compliant                                                                    | RoHS 2015:                          |
| View                                                                         | Certificate of Conformance:         |

## PRODUCT DETAILS

- AR Coated for HeNe Laser Wavelength of 633nm
- Fixed Magnifications Available from 3X to 20X
- Divergence Adjustable with Non-Rotating Optics


TECHSPEC® Arcturus® HeNe Beam Expanders offer high performance optical designs packaged in a precise opto-mechanical platform. Two full rotations of the adjustment knurl provide smooth movement for the optics in order to vary the output from collimated to the minimum focus distance of 1.2 meters. The precise adjustment mechanism keeps optics from rotating, which helps maintain bore sight accuracy and a minimally aberrated beam. Adjustment lock secures position. TECHSPEC® Arcturus® HeNe Beam Expanders are easily secured to both metric and English threaded mounts. Four tapped holes (two M6 on 25mm centers and two 1/4-20 on 1" centers) are located near the middle of the assembly for mounting.

For more cost sensitive applications, Edmund Optics also offers [TECHSPEC Scorpii® Nd:YAG Beam Expanders](#). For applications where rotating optics are acceptable, the [TECHSPEC Vega® Laser Line Beam Expanders](#) and [TECHSPEC Vega® Broadband Beam Expanders](#) are available. For higher precision applications where sliding optics are necessary, please see our [TECHSPEC Draconis® Nd:YAG Laser Line Beam Expanders](#) or [TECHSPEC Draconis® Broadband Beam Expanders](#). For broadband or ultrafast applications, [TECHSPEC Canopus® Reflective Beam Expanders](#) are available.



## TECHNICAL INFORMATION

# Complete Beam Expander



## Beam Expander Mounting Configurations.

Click on an item below to be brought to that item's product page.

