

[See all 22 Products in Family](#)

## 1.67mm FL CS-Mount, Auto Iris, Wide Angle Lens



1.28mm FL C-Mount, Manual Iris, Wide Angle Lens, #62-050



Stock #68-697 [CONTACT US](#)

- 1 + MRP ₹59,320

! Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹59,320 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Low Distortion Wide Angle Lenses **Product Family:**

Fixed Focal Length Lens **Type:**

Auto Iris **Style:**

## Physical & Mechanical Properties

DC Auto Iris **Iris Option:**

56.00 **Length (mm):**

36.0 **Maximum Diameter (mm):**

36 **Outer Diameter (mm):**

80.00 **Weight (g):**

## Optical Properties

110° **Horizontal Field of View, 1/3" Sensor:**

7.20 **Maximum Image Circle (mm):**

1.67 **Focal Length FL (mm):**

100 - ∞ **Working Distance (mm):**

f/1.8 - Closed **Aperture (f/#):**

<1 **Distortion (%):**

<1 **Maximum Distortion (%):**

VIS **Lens Wavelength Range:**

## Sensor

1/2.5" **Maximum Sensor Format:**

4.50 **Pixel Size (µm):**

## Threading & Mounting

N/A **Filter Thread:**

CS-Mount **Mount:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**Compliant** **Reach 211:**

**View** **Certificate of Conformance:**

Indonesia **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

**Note:** Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.