

[See all 22 Products in Family](#)

## 1.8 - 3.0mm FL, C-Mount, Auto Iris, Wide Angle Lens



Image represents #22-793; Design will vary by stock number.

Stock **#22-795** **4 In Stock**

MRP ₹81,774

● Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹81,774 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Product Family:  
Low Distortion Wide Angle Lenses

Type:  
Varifocal Lens

### Physical & Mechanical Properties

Iris Option:  
DC Auto Iris

Length (mm):  
45.30

50	<b>Maximum Diameter (mm):</b>
50	<b>Outer Diameter (mm):</b>
63	<b>Weight (g):</b>

## Optical Properties

120° - 92°	<b>Horizontal Field of View @ Max Sensor Format:</b>
105 - 77°	<b>Horizontal Field of View, 1/3" Sensor:</b>
7.70	<b>Maximum Image Circle (mm):</b>
1.80	<b>Focal Length FL (mm):</b>
300 - ∞	<b>Working Distance (mm):</b>
F/1.8 - Closed	<b>Aperture (f/#):</b>
<1	<b>Distortion (%):</b>
<1	<b>Maximum Distortion (%):</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

1/2.3"	<b>Maximum Sensor Format:</b>
4.50	<b>Pixel Size (µm):</b>

## Threading & Mounting

N/A	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
Indonesia	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

**Note:** Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.