

[See all 3 Products in Family](#)

## 24mm FL Wide Angle Large Format F-Mount Lenses



Wide Angle Large Format F-Mount Lenses

Stock #14-262 **2 In Stock**

MRP ₹1,33,812

**Price inclusive of all taxes**

**ADD TO CART**

### Volume Pricing

Qty 1+	₹1,33,812 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Product Family:**  
Wide Angle Large Format F-Mount Lenses

**Type:**  
Fixed Focal Length Lens

### Physical & Mechanical Properties

**Iris Option:**  
Variable

**Length (mm):**  
95.00

83	<b>Maximum Diameter (mm):</b>
83	<b>Outer Diameter (mm):</b>
565	<b>Weight (g):</b>

## Optical Properties

84.1°	<b>Horizontal Field of View, 35mm Sensor:</b>
61.8°	<b>Horizontal Field of View, APS-C Sensor:</b>
43.30	<b>Maximum Image Circle (mm):</b>
24.00	<b>Focal Length FL (mm):</b>
110 - ∞	<b>Working Distance (mm):</b>
f/1.4 - f/22	<b>Aperture (f/#):</b>
<4	<b>Distortion (%):</b>
<4	<b>Maximum Distortion (%):</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

35mm (43.3mm Image Circle)	<b>Maximum Sensor Format:</b>
----------------------------	-------------------------------

## Threading & Mounting

M77 x0.75	<b>Filter Thread:</b>
F-Mount	<b>Mount:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
South Korea	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Up to 43.3mm Diagonal (35mm Full Frame) Large Format Sensor
- Wide Angles and Large Fields of View
- Lockable Manual Focus and Iris
- 8mm to 24mm Focal Length

Wide Angle Large Format F-Mount Lenses are designed with ultra large fields of view for mid and large format sensors and are ideal for applications requiring short focal lengths. The 8mm focal length lens is designed for creating a fisheye image on APS-C (27.9mm diagonal) sensors, enabling large objects to be in focus throughout the field of view with limited refocusing. Both the 14mm and 24mm focal length lenses are designed for 35mm (43.3mm diagonal) large format sensors. The 14mm lens is versatile with superb image quality even at its full f/2.8 aperture, while the 24mm lens features a fast f/1.4 aperture. Wide Angle Large Format F-Mount Lenses have multi-layer AR coatings to minimize flare and ghosting to ensure excellent image quality and contrast. Each lens features a lockable manual focus and iris.