

TECHSPEC<sup>®</sup> 25/25.4mm Diameter, C-Mount Thin Optic Mount



Stock #56-353 7 In Stock

-

1

+

₹8,482

Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | ₹8,482 each                   |
| Qty 5-9        | ₹7,530 each                   |
| Qty 10-25      | ₹6,950 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Fixed

Type of Optics:

Circular

Function:

| Physical & Mechanical Properties  |                                           |
|-----------------------------------|-------------------------------------------|
| 16.3                              | Extension Length (mm):                    |
| Black Anodized Aluminum (6061 T6) | Construction:                             |
| 20.3                              | Total Length (mm):                        |
| 30.0                              | Outer Diameter (mm):                      |
| 22.00                             | Clear Aperture CA (mm):                   |
| 3.75                              | Max. Thickness of Compatible Optics (mm): |
| 1.0                               | Min. Thickness of Compatible Optics (mm): |

| Threading & Mounting |                                     |
|----------------------|-------------------------------------|
| 25.0 - 25.4          | Diameter of Compatible Optics (mm): |
| C-Mount              | Thread Type:                        |

| Regulatory Compliance               |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | REACH 241:                  |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

25/25.4mm holder is a 3 part assembly and adds 16.3mm to the system length.

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

**Note:** [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

## Technical Information

