

[See all 44 Products in Family](#)

**TECHSPEC® 25.4mm Dia., 355nm T, 532nm R 45° Harmonic Separator**



TECHSPEC Nd:YAG Harmonic Separators

Stock **#37-717** **8 In Stock**

⊖ 1 ⊕ MRP ₹30,469

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹30,469 each
Qty 6-24	₹27,442 each
Qty 25-49	₹24,415 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Harmonic Beamsplitter **Type:**

**Physical & Mechanical Properties**

>85 **Clear Aperture (%):**

**Construction:**

Dichroic

25.40 +0.00/-0.10 **Diameter (mm):**

<3 **Parallelism (arcmin):**

6.35 ±0.20 **Thickness (mm):**

## Optical Properties

45 **Angle of Incidence (°):**

**Coating Specification:**  
Surface 1: R<sub>abs</sub>: >99% @ 532nm, T<sub>abs</sub>: >95% @ 355nm  
Surface 2: R<sub>abs</sub>: <0.5% @ 355nm

532 **Reflection Wavelength (nm):**

**Substrate:**   
[Fused Silica](#) (Corning 7980)

M10 **Surface Flatness (P-V):**

10-5 **Surface Quality:**

355 **Transmission Wavelength (nm):**

**Damage Threshold, Reference:**   
Surface 1:  
5 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz  
2.5 J/cm<sup>2</sup> @ 355nm, 20ns, 20Hz  
Surface 2:  
7.5 J/cm<sup>2</sup> @ 355nm, 20ns, 20Hz

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 209:**

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

**Note:** The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.

## Compatible Mounts