

TECHSPEC® 30R/70T NIR, C-Mounted Plate Beamsplitter



Stock #49-687 [CONTACT US](#)

- 1 + MRP ₹33,697

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹33,697 each
Qty 5-9	₹29,460 each
Qty 10+	₹27,644 each
Need More?	Request Quote

Product Downloads

General

Standard Beamsplitter **Type:**

Beamsplitter Included:
[Standard 30R/70T NIR Plate Beamsplitter, 1 λ](#)

Physical & Mechanical Properties

Plate **Construction:**

+0.0/-0.25	Dimensional Tolerance (mm):
38.0	Extension Length (mm):
Black Anodized Aluminum	Housing:
38 x 38 x 50	Housing Dimension:

Optical Properties

Surface 2: Multi-Layer Anti-Reflection for Near-Infrared Region	Coating Specification:
30/70	Reflection/Transmission Ratio (R/T):
±5	Reflection/Transmission Tolerance (%):
N-BK7	Substrate: <input type="checkbox"/>
1λ	Surface Flatness (P-V):
60-40	Surface Quality:
700 - 1100	Wavelength Range (nm):

Threading & Mounting

C-Mount Enclosure	Mount:
C-Mount (1" x 32 TPI)	Thread Type:

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Pre-Mounted 90 Degree Interface
- Four C-Threaded Mounting Holes
- Several Beamsplitting Options Available
- Additional C-Mounted [Beamsplitters](#), [Filters](#), and [Mirrors](#) Available

TECHSPEC® C-Mounted Plate Beamsplitters are designed to simplify system integration. These mounted beamsplitters include a TECHSPEC® Plate Beamsplitter pre-mounted in an Aluminum cube designed to interface with C-Mount (1" x 32 TPI) systems. Each cube is configured with four C-threaded holes, one on each face, and a ¼-20 tapped hole on the base for post mounting. TECHSPEC® C-Mounted Plate Beamsplitters are available in 30R/70T, 50R/50T, and 70R/30R options for either the visible or near infrared spectrum.

The C-Mounted Visible Plate Beamsplitters are designed for the 400 - 700nm wavelength range and the C-Mounted NIR Plate Beamsplitters are designed for the 700 - 1100nm wavelength range.

Note: These products cannot be disassembled. For mounting an alternative beamsplitter in a C-Mount Cube, use either [#56-264](#) or [#56-265](#).

Technical Information

