

[See all 36 Products in Family](#)

## 400nm, 6 x 6mm, OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock **#15-198** **20+ In Stock**

MRP ₹5,045

**Price inclusive of all taxes**

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹5,045 each
Qty 10-25	₹4,541 each
Qty 26-49	₹4,237 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Longpass Filter **Type:**

### Physical & Mechanical Properties

6.00 x 6.00 +0.00/-0.20 **Dimensions (mm):**

**Length (mm):**

6.00

2.00 ±0.10

Thickness (mm):

6.00

Width (mm):

90

Clear Aperture (%):

ML-C-48497A, Section 3.4.1

Physical Durability:

## Optical Properties

0

Angle of Incidence (°):

≥2.0

Optical Density OD (Average):

400.00 ±8

Cut-On Wavelength (nm):

BOROFLOAT®

Substrate:

Hard Coated

Coating:

200 - 375

Rejection Wavelength (nm):

60-40

Surface Quality:

≥85

Transmission (%):

425 - 1600

Transmission Wavelength (nm):

200 - 1600

Wavelength Range (nm):

## Environmental & Durability Factors

ML-STD-810F, Section 507.4

Environmental Durability:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

United States

Country of Origin:

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- Sharp Cut-On Wavelength
- ≥85% Transmission and OD 2.0 Blocking
- 6mm Square or 12.5/25mm Diameter Sizes
- [TECHSPEC® OD 4.0 Longpass Filters](#) Also Available

OD 2.0 Longpass Filters are cost-effective filters with cut-on wavelengths ranging from 400 to 950nm. These longpass filters provide ≥85% transmission across a transmission band that extends out to 1600nm while providing OD 2.0 blocking across their rejection band. The back surface of each filter is coated with an antireflection (AR) coating, increasing the overall efficiency of the filter. OD 2.0 Longpass Filters can be combined with OD 2.0 Shortpass Filters to create custom bandpass filters to meet application requirements in the visible or near-infrared. These longpass filters are ideal for use in fluorescence applications or separating spectral orders, with the 6 x 6mm sized filters suitable for integration into optical instrumentation requiring cost-effective, lightweight filters.

## Technical Information

### OD 2.0 Longpass Filters



### Compatible Mounts

---