

## 4" x 4" Size, Plastic Optical Window



Stock #71-532 **15 In Stock**

- 1 + MRP ₹4,843

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-49	₹4,843 each
Qty 50-99	₹3,834 each
Qty 100-199	₹3,632 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Protective Window **Type:**

#### Physical & Mechanical Properties

4.00 x 4.00 ±0.01 **Dimensions (inches):**

101.60 x 101.60 ±0.25 **Dimensions (mm):**

1.50 ±0.15	<b>Thickness (mm):</b>
101.60	<b>Length (mm):</b>
101.60	<b>Width (mm):</b>

## Optical Properties

Uncoated	<b>Coating:</b>
Thermoset ADC (CR-39®)	<b>Substrate:</b> <input type="checkbox"/>
1.501	<b>Index of Refraction (n<sub>d</sub>):</b>
>90 (typical)	<b>Transmission (%):</b>
59.2	<b>Abbe Number (v<sub>d</sub>):</b>
400 - 1500	<b>Wavelength Range (nm):</b>

## Material Properties

1.320	<b>Density (g/cm<sup>3</sup>):</b>
-------	------------------------------------

## Environmental & Durability Factors

100 Continuous, 130 for 1 hour	<b>Operating Temperature (°C):</b>
--------------------------------	------------------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 242:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Lightweight Alternative to Glass Windows
- Excellent Thermal and Chemical Resistance
- Higher Transmission than Similar Transparent Plastics

Clear Optical Cast Plastic Windows are a lightweight and durable option compared to a glass alternative. These windows have a high transmission and low haze, have 25 - 50 times greater abrasion resistance, and are resistant to all types of chemicals and solvents (acetone, acids, alkali and alcohols). Due to their construction, these windows are able to be drilled using a carbide bit for various mounting needs.

Clear Optical Cast Plastic Windows are uncoated, and are available in circular, rectangular, and square options.

## Technical Information

**Thermoset ADC (CR-39®)**  
**Typical Transmission**

