

TECHSPEC® 50.0/50.8mm Optic Dia., Kinematic Mount, 3-Screws



50/50.8mm Diameter Kinematic Mount, 3-Screws, #58-855

Stock **#58-855** 20+ In Stock

-

1

+

₹10,636

ADD TO CART

Volume Pricing	
Qty 1-4	₹10,636 each
Qty 5-9	₹9,572 each
Qty 10+	₹8,831 each
Need More?	Request Quote

Product Downloads

General	
Adjustable - Tip-Tilt	Type:
Circular	Type of Optics:
3	Number of Adjustment Screws:
Available in Quick Start Kit: #17-524	Note:

Physical & Mechanical Properties	
45.9	Clear Aperture CA (mm):
Z-Axis: 12	Travel (mm):
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings	
±5	Fine Tilt Angle (°):
±5	Fine Tip Angle (°):
2.3	Sensitivity per 1° Knob Rotation (arcsec):
0.25	Adjustment Screw Pitch (mm):
2.0	Min. Thickness of Compatible Optics (mm):
1.3	Pointing Stability (μrad):

Optical Properties	
0.2 per 0.25mm turn	Angle Tolerance (°):

Threading & Mounting	
50.0 - 50.8	Size of Compatible Optics (mm):
M4 x0.7, 8-32	Compatible Post:

Environmental & Durability Factors	
<5	Thermal Stability (μrad):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- 100 TPI Fine Adjustment Screws
 - Finger Cuts for Convenience and Accuracy
 - Tip/Tilt Range:±5°
- TECHSPEC® Kinematic Optical Mirror Mounts allow precise and accurate adjustment of optical components in a wide range of applications. Each mount features high-accuracy adjustment screws, in either two-screw or three-screw versions, for control of tip and tilt. The three-screw versions specifically allow for additional translation in the optical axis. TECHSPEC® Kinematic Optical Mirror Mbunts contain nylon-tipped locking screws (1.5mm hex key included) that prevent damage to the optics and incorporate finger cuts to make the placement of optical components convenient and accurate.
- Construction materials ensure quality and repeatability. Stainless steel inserts are used for all adjustment screw contact surfaces and specially designed dampening grease provides smooth movement. Adjustment knobs are removable for Allen Key or motorized adjustment (2mm key size). Included hardware kit contains post-mounting screws and Allen wrenches for adjustment.
- These mounts are designed to connect to our [TECHSPEC® Metric Stainless Steel Mounting Posts](#). When the male-thread adapter is removed from the post, either an M4 or 8-32 tapped hole is available to accept the post-mounting screw from the mount.
- [TECHSPEC® Optical Mount Accessories](#) are available to easily integrate TECHSPEC® Kinematic Optical Mirror Mbunts into a variety of application setups.