

TECHSPEC®

50.8mm Dia. Protected Aluminum Coated, Mounted Fused Silica Corner Cube Retroreflector



Mounted Fused Silica Corner Cube Retroreflectors

Stock **#15-822** **2 In Stock**

MRP ₹69,614

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹69,614 each
Qty 6-25	₹55,995 each
Qty 26-49	₹51,959 each
Need More?	Request Quote

Product Downloads

General

Retroreflector **Type:**

Physical & Mechanical Properties

Inner Diameter (mm):

50.8 +0.0/-0.1

Outer Diameter (mm):

63.5

Housing Tolerance (mm):

Outer Diameter: +0/-0.5, Height: ±0.25

Optical Properties

Beam Deviation (arcsec):

±3

Coating:

Aluminum with protective overcoat

Substrate:

[Fused Silica](#) (Coming 7980)

Surface Quality:

20-10

Image Orientation:

Left-Handed

Coating Specification:

Reflective Surfaces: $R_{avg} > 85\%$ FROM 400-700nm, @ 45° AOI

Ray Deviation (°):

180

Wavelength Range (nm):

400 - 700

Power (fringes) @ 632.8nm:

0.20

Irregularity (fringes) @ 632.8nm:

0.20

Threading & Mounting

Mounting Threads:

(2) ¼-20 Tapped Holes

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:


Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details


- ¼-20 Tapped Holes for Easy Mounting
- Excellent Transmission in the UV
- Useful for Surveying and Alignment
- Also Available [Unmounted](#)

TECHSPEC® Mounted Fused Silica Corner Cube Retroreflectors are pre-mounted in anodized aluminum housings with two ¼-20 tapped holes for easy integration into optical systems. Corner cube retroreflectors are designed to reflect any ray or beam entering the prism face, regardless of the orientation of the prism, back onto itself. Mirrors will only do this at a normal angle of incidence, making corner cube retroreflectors better suited for applications where precision alignment is difficult or time-consuming. TECHSPEC Mounted Fused Silica Corner Cube Retroreflectors are ideal for prototyping or research applications that require convenient, durable mounting solutions. These mounted retroreflectors provide excellent transmission in the UV.

Technical Information



Stock No.	Inner Diameter ID	Outer Diameter OD	H	X
#15-817	12.7	31.75	11.73	18.08
#15-818	12.7	31.75	11.73	18.08
#15-819	25.4	38.10	20.62	26.98
#15-820	25.4	38.10	20.62	26.98
#15-821	50.8	63.50	39.95	46.30
#15-822	50.8	63.50	39.95	46.30



Units: mm