


TECHSPEC® 5.0mm Diameter, LASFN-35 Ball Lens



Stock #47-130 20+ In Stock

-

1

+

₹7,201

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹7,201 each                   |
| Qty 11-49      | ₹6,500 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                          |
|----------------------------------|--------------------------|
| Ball Lens                        | Type:                    |
| Physical & Mechanical Properties |                          |
| 5.00                             | Diameter (mm):           |
| +0/-3                            | Diameter Tolerance (µm): |
| Optical Properties               |                          |

|                                     |                                        |
|-------------------------------------|----------------------------------------|
| LASFN-35                            | Substrate: <input type="checkbox"/>    |
| Uncoated                            | Coating:                               |
| 400 - 2400                          | Wavelength Range (nm):                 |
| 2.022                               | Index of Refraction (n <sub>d</sub> ): |
| 2.00                                | Sphericity (μm):                       |
| Regulatory Compliance               |                                        |
| Compliant                           | RoHS 2015:                             |
| View                                | Certificate of Conformance:            |
| Compliant                           | Reach 247:                             |
| Switzerland                         | Country of Origin:                     |
| Edmund Optics India Private Limited | Imported By:                           |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- 2.0 Index of Refraction
- High Tolerance
- [High Index Half-Ball Lenses](#) Also Available

TECHSPEC® High Index Ball Lenses provide for a shorter back focal length, simplifying fiber coupling, due to the high index of refraction. Ball lenses are manufactured from a single glass substrate and can either focus or collimate light. The LASFN-35 substrate has an Abbe Number of 29.06, density of 5.41g/cm<sup>3</sup>, and coefficient of linear expansion of 7.4 microns/°K (-30 to 70°C). TECHSPEC® High Index Ball Lenses are ideal for endoscopy, bar code scanning, ball pre-forms for aspheric lenses, and sensor applications.

## Compatible Mounts