

TECHSPEC® 8" Length, 8-32 Stud, Steel Post



Stock #58-967 CLEARANCE 3 In Stock

1 - + MRP ₹1,270

! Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,270 each
Need More?	Request Quote

Product Downloads

STEP:step	PDF Drawing:pdf
IGES:igs	eDrawing:eprt
EO Spec Sheet	Download All

General	
Type: English	
Physical & Mechanical Properties	
Length (mm): 203.20	Length (inches): 8.0
Diameter (mm): 12.70	Diameter (inches): 0.5
Threading & Mounting	
Male Thread: 8-32	
Regulatory Compliance	
RoHS 2015: Compliant	Certificate of Conformance: View
REACH 241: Compliant	
Country of Origin: China	Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000

Product Details

Adapter #58-982 is included. Additional [thread adapters](#) available separately.

- Male 8-32 or 1/4-20 Stud, Female 1/4-20 Base
- Posts Include Interchangeable Male Stud and Removable Base S.H.S.S.
- Available in Variety of Lengths
- [Metric Versions Also Available](#)

TECHSPEC® English Stainless Steel Mounting Posts include a ¼" long male thread stud adapter that is easily interchangeable with other adapters to ensure compatibility between these posts and any optical mount. Removing the included adapter reveals female 8-32 threads on the post. Each optical post also has a thru-hole to allow an Allen wrench or other tool to rotate the post easily. Thread values are laser engraved on each post for quick identification and integration. TECHSPEC English Stainless Steel Mounting Posts are offered in a variety of lengths. [Metric Versions are also available for purchase.](#)

Technical Information

#68-230		
Stock No.	Description	Qty
#59-751	Steel Post, 1" Length	1
#59-752	Steel Post, 1.5" Length	1
#58-999	Steel Post, 2" Length	2
#59-754	Steel Post, 3" Length	2
#59-000	Steel Post, 4" Length	2
#59-008	Steel Post, 6" Length	1
#59-009	Steel Post, 8" Length	1

#68-229		
Stock No.	Description	Qty
#58-960	Steel Post, 1" Length	1
#58-961	Steel Post, 1.5" Length	1
#58-962	Steel Post, 2" Length	2
#58-964	Steel Post, 3" Length	2
#58-965	Steel Post, 4" Length	2
#58-966	Steel Post, 6" Length	1
#58-967	Steel Post, 8" Length	1

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	¼-20 Stud, English Post Kit		#68-230 CLEARANCE	₹5,730 Request Quote	CONTACT US <input type="text" value="1"/>

Related Products



Metric Stainless Steel Mounting Posts



Post Holders



Post Holder Assemblies



Adjustable Height Post Holders

Frequently Purchased Together



#03-655 - Sliding 2" x 3" Base Plate
₹2,548

Qty



#03-666 - 8.0 - 118.0 Optic Height,
English Bar-Type Optic Holder
₹12,107

Qty



#03-640 - 24" x 12", Breadboard
₹39,045

Qty



#03-644 - 1/4-20 x 1/2"
Setscrew, 12/Pack
₹1,237

Qty



Resources

Media Type

- FAQ
- Glossary
- Application Note
- Trending in Optics
- Video

? FAQ

Do you have
any
components
that would...

? FAQ

Do your iris
diaphragms
have
mounts for...

GLOSSARY

Axial Runout

GLOSSARY

Concentricity

GLOSSARY

Inverted Load
Capacity

GLOSSARY

Tangent Arm
Drive

View More