

**TECHSPEC® 8" Length, 1/4-20 Stud, Steel Post**



Stock **#59-009** CLEARANCE CONTACT US

MRP ₹1,539

Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹1,539 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

English Type:

**Physical & Mechanical Properties**

203.20 Length (mm):

8.0 Length (inches):

12.70 Diameter (mm):

Diameter (inches):

0.5

## Threading & Mounting

Male Thread:

1/4-20

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

REACH 241:

Compliant

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details

Adapter #58-983 is included. Additional [thread adapters](#) available separately.

- Male 8-32 or 1/4-20 Stud, Female 1/4-20 Base
- Posts Include Interchangeable Male Stud and Removable Base S.H.S.S.
- Available in Variety of Lengths
- [Metric Versions Also Available](#)

TECHSPEC® English Stainless Steel Mounting Posts include a 1/4" long male thread stud adapter that is easily interchangeable with other adapters to ensure compatibility between these posts and any optical mount. Removing the included adapter reveals female 8-32 threads on the post. Each optical post also has a thru-hole to allow an Allen wrench or other tool to rotate the post easily. Thread values are laser engraved on each post for quick identification and integration. TECHSPEC English Stainless Steel Mounting Posts are offered in a variety of lengths. [Metric Versions are also available for purchase.](#)

## Technical Information



| #68-230   |                         |     |
|-----------|-------------------------|-----|
| Stock No. | Description             | Qty |
| #59-751   | Steel Post, 1" Length   | 1   |
| #59-752   | Steel Post, 1.5" Length | 1   |
| #58-999   | Steel Post, 2" Length   | 2   |
| #59-754   | Steel Post, 3" Length   | 2   |
| #59-000   | Steel Post, 4" Length   | 2   |
| #59-008   | Steel Post, 6" Length   | 1   |
| #59-009   | Steel Post, 8" Length   | 1   |

| #68-229   |                         |     |
|-----------|-------------------------|-----|
| Stock No. | Description             | Qty |
| #58-960   | Steel Post, 1" Length   | 1   |
| #58-961   | Steel Post, 1.5" Length | 1   |
| #58-962   | Steel Post, 2" Length   | 2   |
| #58-964   | Steel Post, 3" Length   | 2   |
| #58-965   | Steel Post, 4" Length   | 2   |
| #58-966   | Steel Post, 6" Length   | 1   |
| #58-967   | Steel Post, 8" Length   | 1   |