

90° Angle Mount



#39-355 90° Angle Mount

Stock **#39-355** 14 In Stock

-

1

+

₹5,318

ADD TO CART

Volume Pricing	
Qty 1+	₹5,318 each
Need More?	Request Quote

Product Downloads

General

Mounting Adapter

Type:

Physical & Mechanical Properties

63.5 x 50.8 x 38.1

Dimensions (mm):

Black Stainless Steel

Construction:

2

Weight (lbs):

2½L x2 Wx1½H		Dimensions (inches):
Threading & Mounting		
3/4-16		Mounting Threads:
Regulatory Compliance		
Compliant		RoHS 2015:
View		Certificate of Conformance:
Compliant		Reach 250:
United States		Country of Origin:
Edmund Optics India Private Limited		Imported By:

Product Details

• Swivel Arm for Added Flexibility

• 90° Angle Mounts Connect Horizontal Arms onto Vertical Posts

• Ring Mounts for Increased Versatility


• [Imaging System Bases](#), [Rack and Pinion Focusing Mounts](#), and [Stainless Steel Posts](#) Also Available

Accessories for Imaging Systems are available to increase the versatility of an imaging system. Products in this family include a swivel arm, Infinity Microscope, 90° angle mount, and ring mounts. The swivel arm adds an axis of rotation to the rack and pinion-focusing mounts. The swivel arm can rotate around a vertical post, and the rack and pinion focus mount can rotate around the ¼" post attached to the swivel arm. The Infinity microscope mounting adapter is compatible with Rack and Pinion Mount [#39-357](#) and reduces the thru hole diameter to 58mm. The 90° angle mount, offered in Accessories for Imaging Solutions, allows the mounting of posts at 90° in optical systems. Ring mounts are available for attaching light sources, articulating arms, straight posts, or any ¼-20 accessory to standard mounting hardware.

Features

90° Angle Mount [#39-355](#) features two ¾" thru holes at 90° with locking knobs. All Ring Mounts feature ¼-20 mounting hole, set screw for securing post, or optical component within the inner diameter. Swivel Arm [#03-684](#) features a 0.75" diameter post which accepts rack and pinion focusing mount and allows swivel movement. Infinity Mounting Adapter [#39-358](#) features male and female T-thread to replace 24mm tube section of infinity lens.

Technical Information



Stock No.	A	T	O.D.	I.D.
#54-263	0.375"	0.5"	2.5"	1.5"
#54-264	0.375"	0.5"	1.75"	0.75"
#54-265	0.271"	0.375"	1.25"	0.5"

Units: inches